

## KT-LED13A19-0-8XX REPLACEMENT LAMP

### DESCRIPTION

13W A19 Lamp | 2700–5000K | >80 CRI | Omni-Directional



<b>LAMP TYPE:</b> A19
<b>BASE TYPE:</b> E26 (Medium)
<b>WATTAGE:</b> 13W
<b>COLOR TEMPERATURE:</b> 2700–5000K
<b>COLOR RENDERING INDEX (CRI):</b> >80
<b>WARRANTY:</b> 3 Years
<b>RATED LIFE:</b> L70 (25,000 Hours)



### TYPICAL APPLICATIONS

- Table, Desk, and Floor Lamps
- Wall Sconces
- Surface Mount Ceiling Fixtures
- General Lighting
- Pendant Lights

### PRODUCT FEATURES


- Energy Efficient, 80%+ Energy Savings over Legacy Equivalents
- Lower Heat Generation than Legacy Equivalents
- PF >0.70
- Complies with Part 15 of FCC
- Durable Plastic housing lowers the risk for breakage
- ANSI compliant construction ensures fitment for intended applications
- Rated for open, recessed, and enclosed fixtures
- Operating temperature range –4°F/–20°C to 95°F/35°C
- Long Life minimizes replacement and maintenance costs
- Meets Energy Star requirements
- UL Listed
- Smooth diffused lens for comfortable glare free performance
- Smooth, uniform dimming
- Suitable for damp locations

### ELECTRICAL AND PERFORMANCE SPECIFICATIONS

Keystone Catalog Number	Description	Color Temp	Input Voltage	Rated Lamp Wattage	Legacy Equivalent Wattage	Base Type	Lumens	CRI	Beam Angle	Dimmable	Efficacy
KT-LED13A19-0-827	A19 bulb. Omni-Directional, dimmable	2700K	120V	13W	100W	E26	1600	>80	230°	Yes	123 lm/W
KT-LED13A19-0-830	A19 bulb. Omni-Directional, dimmable	3000K	120V	13W	100W	E26	1600	>80	230°	Yes	123 lm/W
KT-LED13A19-0-835	A19 bulb. Omni-Directional, dimmable	3500K	120V	13W	100W	E26	1600	>80	230°	Yes	123 lm/W
KT-LED13A19-0-840	A19 bulb. Omni-Directional, dimmable	4000K	120V	13W	100W	E26	1600	>80	230°	Yes	123 lm/W
KT-LED13A19-0-850	A19 bulb. Omni-Directional, dimmable	5000K	120V	13W	100W	E26	1600	>80	230°	Yes	123 lm/W

**KT-LED13A19-O-8XX**  
REPLACEMENT LAMP

**PHYSICAL CHARACTERISTICS**



**PACKAGING**

Carton Quantity	60 pcs
Carton Dimensions	24.61" × 14.76" × 5.31"
Carton Weight	17.15 lbs

**LAMP DIMENSIONS**

A (Length)	4.57"
B (Diameter)	2.36"

BASE TYPE: E26 (Medium)

**ORDERING INFORMATION**

CATALOG NUMBER	CARTON QUANTITY	EASY CODE	UPC
KT-LED13A19-O-827	60 pcs	FWO-45	843654130248
KT-LED13A19-O-830	60 pcs	TGB-97	843654130255
KT-LED13A19-O-835	60 pcs	MAQ-54	843654130262
KT-LED13A19-O-840	60 pcs	RMC-77	843654130279
KT-LED13A19-O-850	60 pcs	JRR-45	843654130286

**CATALOG NUMBER BREAKDOWN**

**KT-LED13A19-O-8XX**

1 2 3 4 5 6 7

- 1 Keystone Technologies
- 2 LED Lamp
- 3 Wattage
- 4 Lamp Shape
- 5 Omni-Directional
- 6 800 Series
- 7 Color Temperature

## KT-LED13A19-0-8XX REPLACEMENT LAMP

### DESCRIPTION

13W A19 Lamp | 2700–5000K | >80 CRI | Omni-Directional



RoHS  
Compliant

**3YEAR**  
WARRANTY

<b>LAMP TYPE:</b> A19
<b>BASE TYPE:</b> E26 (Medium)
<b>WATTAGE:</b> 13W
<b>COLOR TEMPERATURE:</b> 2700–5000K
<b>COLOR RENDERING INDEX (CRI):</b> >80
<b>WARRANTY:</b> 3 Years
<b>RATED LIFE:</b> L70 (25,000 Hours)



### TYPICAL APPLICATIONS

- Table, Desk, and Floor Lamps
- Wall Sconces
- Surface Mount Ceiling Fixtures
- General Lighting
- Pendant Lights

### PRODUCT FEATURES


- Energy Efficient, 80%+ Energy Savings over Legacy Equivalents
- Lower Heat Generation than Legacy Equivalents
- PF >0.70
- Complies with Part 15 of FCC
- Durable Plastic housing lowers the risk for breakage
- ANSI compliant construction ensures fitment for intended applications
- Rated for open, recessed, and enclosed fixtures
- Operating temperature range –4°F/–20°C to 95°F/35°C
- Long Life minimizes replacement and maintenance costs
- Meets Energy Star requirements
- UL Listed
- Smooth diffused lens for comfortable glare free performance
- Smooth, uniform dimming
- Suitable for damp locations

### ELECTRICAL AND PERFORMANCE SPECIFICATIONS

Keystone Catalog Number	Description	Color Temp	Input Voltage	Rated Lamp Wattage	Legacy Equivalent Wattage	Base Type	Lumens	CRI	Beam Angle	Dimmable	Efficacy
KT-LED13A19-0-827	A19 bulb. Omni-Directional, dimmable	2700K	120V	13W	100W	E26	1600	>80	230°	Yes	123 lm/W
KT-LED13A19-0-830	A19 bulb. Omni-Directional, dimmable	3000K	120V	13W	100W	E26	1600	>80	230°	Yes	123 lm/W
KT-LED13A19-0-835	A19 bulb. Omni-Directional, dimmable	3500K	120V	13W	100W	E26	1600	>80	230°	Yes	123 lm/W
KT-LED13A19-0-840	A19 bulb. Omni-Directional, dimmable	4000K	120V	13W	100W	E26	1600	>80	230°	Yes	123 lm/W
KT-LED13A19-0-850	A19 bulb. Omni-Directional, dimmable	5000K	120V	13W	100W	E26	1600	>80	230°	Yes	123 lm/W

**KT-LED13A19-O-8XX**  
REPLACEMENT LAMP

**PHYSICAL CHARACTERISTICS**



**PACKAGING**

Carton Quantity	60 pcs
Carton Dimensions	24.61" × 14.76" × 5.31"
Carton Weight	17.15 lbs

**LAMP DIMENSIONS**

A (Length)	4.57"
B (Diameter)	2.36"

BASE TYPE: E26 (Medium)

**ORDERING INFORMATION**

CATALOG NUMBER	CARTON QUANTITY	EASY CODE	UPC
KT-LED13A19-O-827	60 pcs	FWO-45	843654130248
KT-LED13A19-O-830	60 pcs	TGB-97	843654130255
KT-LED13A19-O-835	60 pcs	MAQ-54	843654130262
KT-LED13A19-O-840	60 pcs	RMC-77	843654130279
KT-LED13A19-O-850	60 pcs	JRR-45	843654130286

**CATALOG NUMBER BREAKDOWN**

**KT-LED13A19-O-8XX**

- 1
- 2
- 3
- 4
- 5
- 6
- 7

- 1 Keystone Technologies
- 2 LED Lamp
- 3 Wattage
- 4 Lamp Shape
- 5 Omni-Directional
- 6 800 Series
- 7 Color Temperature