



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

LED13T8L48DIM841 *Delisted* 13W Led T8 48" 41K FRST GLS

Sylvania-Ledvance

Catalog Number	LED13T8L48DIM841
Manufacturer	Sylvania-Ledvance
Description	OBS75510 4FT Substitubeled T8, Frosted Glass, 13W, Dimmable, 82CRI, 2100 Lumen, 4100K, 60000 Life
Weight per unit	0.5608 (lbs/each)
Product Category	Shape & Circular Lamps

Features

average life	60000
Base	Medium Bipin
Lamp Type	LED T8
lumens	2,100
Shape	T8
Voltage	120.00 - 277.00 V
Wattage	13.00

Material, Color, and Finish

color rendering index (cri)	82
color temperature	4100
Style	Tube, double-ended

Dimensions and Weight

Size	1
------	---

Descriptions

Description	*DELISTED* 13W LED T8 48" 41K FRST GLS
extra long description	SYL LED13T8L48DIM841SUBG8/75510 LED
Long Description	OBS75510 4ft SubstiTUBELED T8, frosted glass, 13W, Dimmable, 82CRI, 2100 Lumen, 4100K, 60000 life
Product Type	LED13T8L48DIM841SUBG8 25/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135755101
Manufacturers Part Number	LED13T8L48DIM841SUBG8/75510
sub brand	SubstiTUBE
UPC	046135755101

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

Availability

Status	Inactive
--------	----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	25
Weight Per each	0.5608

Uses, Certifications, and Standards

standard	cULus
----------	-------