



## LED14BDT8G4850 14W Led T8 48" 50K DBL Ended Line Voltage - Glass *Ge By Current Lamps*

Catalog Number	LED14BDT8G4850
Manufacturer	Ge By Current Lamps
Description	Led Type B Double Ended T8 Glass Tube
Weight per unit	0.5300 (lbs/each)
Product Category	Shape & Circular Lamps

### Descriptions

Description	14W LED T8 48" 50K DBL ENDED LINE VOLTAGE - GLASS
extra long description	DOUBLE ENDED, BALLAST BYPASS, B TYPE; 48 INCH; UL, DLC APPROVAL; DAMP LOCATION APPLICATION; 120 TO 277 VOLT VOLTAGE RATING; 14 WATT WATTAGE; LED GLASS TUBE; G13 BASE TYPE; 50000 LIFE IN HOUR; GLASS BASE MATERIAL; T8 SHAPE DESIGNATION; 1850 LUMEN INTENSITY; 5000; 80 COLOR RENDERING INDEX; ROHS COMPLIANT; POWER FACTOR GREATER THAN 0.9
Long Description	LED TYPE B DOUBLE ENDED T8 GLASS TUBE
Product Type	Linear Fluorescent Led Lamp

### Manufacturer Information

Brand	Ge Led Lamps
GTIN	10043168395196
Manufacturers Part Number	LED14BDT8G4850
UPC	043168395199

### Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

### Packaging

Carton	1
Package	20
Weight Per each	0.53