



GE
Lighting

35911 - Integrated 4 ft Value LED Glass Tubes

LED15ET8/850-V6P

- ☞ Convert your existing linear fluorescent fixture to LED lighting without needing a comprehensive reinstall.
- ☞ Each LED tube is outfitted with an internal GE driver.
- ☞ The GE integrated LED tubes run on electronic T8 instant-start or programmed start ballasts.
- ☞ 66% longer life than LFL (50,000 vs. 30,000 hours)
- ☞ No UV
- ☞ Easy disposal, non-hazardous waste
- ☞ Check ballast compatibility at www.gelighting.com/LEDTUBES-ballast-compatibility
- ☞ UL Listed

Product Photo



GENERAL CHARACTERISTICS

Product Technology	LED
Rated Life (Hours)	50000 h
LED Tube Type	Glass
Environmental Rating	LED_Tube_Glass
10 Digit U	4316835911
Lamp Count	1
Life in Years	45.7 yr
Requested Structure	Sleeve, Carton
Estimated Energy Cost per Year	1.81
Bulb Shape	T8

PHOTOMETRIC CHARACTERISTICS

Rated Beam Spread	15 W
Initial Lumens-nominal	1800 lm
Color Temperature	5000 K

PRODUCT INFORMATION

Product Code	35911
Description	LED15ET8/850-V6P
Alternative Unit Of Measure	EACH
Standard Package Quantity	6
Ean UPC	043168359115
Standard Package GTIN	00043168359115
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
Sales Unit	Each
UCC	043168359115
Alternative Unit Of Measure	CASE
Standard Package Quantity	6
Ean UPC	043168359115
Standard Package GTIN	10043168359112
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
Sales Unit	Case
UCC	043168359115

DIMENSIONS

Bulb Max Overall Length-MOL	48.0 in
-----------------------------	---------

ELECTRICAL CHARACTERISTICS

Drive Current	45.7
Energy Efficiency Class	yr
Voltage <Nom>	120 V
Rated power (Watts)	15 W

CAUTIONS & WARNINGS

Caution

Risk of fire

Use only in place of fluorescent lamps specified on label

If the lamp or luminaire exhibits undesirable operation, immediately turn off power, remove lamp from luminaire and contact manufacturer

Direct replacement for 25W/48T8, 28W/48T8, 30W/48T8, 32W/48T8 lamps only

Do not install this lamp in a pre-heat luminaire

This lamp only operates on electronic ballasts

If lamp does not light when luminaire is energized, remove lamp from luminaire and contact lamp manufacturer or qualified electrician

Risk of electric shock

Suitable for damp locations

Not intended for use with emergency exit fixtures or emergency exit lights



GE
Lighting

35911 - Integrated 4 ft Value LED Glass Tubes

LED15ET8/850-V6P

- ☞ Convert your existing linear fluorescent fixture to LED lighting without needing a comprehensive reinstall.
- ☞ Each LED tube is outfitted with an internal GE driver.
- ☞ The GE integrated LED tubes run on electronic T8 instant-start or programmed start ballasts.
- ☞ 66% longer life than LFL (50,000 vs. 30,000 hours)
- ☞ No UV
- ☞ Easy disposal, non-hazardous waste
- ☞ Check ballast compatibility at www.gelighting.com/LEDTUBES-ballast-compatibility
- ☞ UL Listed

Product Photo



GENERAL CHARACTERISTICS

Product Technology	LED
Rated Life (Hours)	50000 h
LED Tube Type	Glass
Environmental Rating	LED_Tube_Glass
10 Digit U	4316835911
Lamp Count	1
Life in Years	45.7 yr
Requested Structure	Sleeve, Carton
Estimated Energy Cost per Year	1.81
Bulb Shape	T8

PHOTOMETRIC CHARACTERISTICS

Rated Beam Spread	15 W
Initial Lumens-nominal	1800 lm
Color Temperature	5000 K

PRODUCT INFORMATION

Product Code	35911
Description	LED15ET8/850-V6P
Alternative Unit Of Measure	EACH
Standard Package Quantity	6
Ean UPC	043168359115
Standard Package GTIN	00043168359115
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
Sales Unit	Each
UCC	043168359115
Alternative Unit Of Measure	CASE
Standard Package Quantity	6
Ean UPC	043168359115
Standard Package GTIN	10043168359112
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
Sales Unit	Case
UCC	043168359115

DIMENSIONS

Bulb Max Overall Length-MOL	48.0 in
-----------------------------	---------

ELECTRICAL CHARACTERISTICS

Drive Current	45.7
Energy Efficiency Class	yr
Voltage <Nom>	120 V
Rated power (Watts)	15 W

CAUTIONS & WARNINGS

Caution

Risk of fire

Use only in place of fluorescent lamps specified on label

If the lamp or luminaire exhibits undesirable operation, immediately turn off power, remove lamp from luminaire and contact manufacturer

Direct replacement for 25W/48T8, 28W/48T8, 30W/48T8, 32W/48T8 lamps only

Do not install this lamp in a pre-heat luminaire

This lamp only operates on electronic ballasts

If lamp does not light when luminaire is energized, remove lamp from luminaire and contact lamp manufacturer or qualified electrician

Risk of electric shock

Suitable for damp locations

Not intended for use with emergency exit fixtures or emergency exit lights

