



# KT-LED15T8-48GC-835-S

T8 LED LAMP

### **DESCRIPTION**

15W T8 LED | 3500K | >80 CRI | High Efficiency | Ballast Compatible
















- Compatible with Most Instant and Program Start Electronic T8 Ballasts,
  Contact Keystone for Ballast Compatibility List
- Direct Replacement for the Following Fluorescent Lamps: F32T8/32W, F32T8/30W, F32T8/28W, F32T8/25W
- UL Listed; Listed on DLC Qualified Product List
- 50,000+ Hour Lifetime
- Environmentally Friendly: No Mercury Used
- Instant Startup
- Frosted Lens Eliminates Pixelation





- Operating Temperature: -20°C/-4°F to 45°C/113°F
- 110+ Lumens per Watt (Bare Lamp Efficacy)
- Suitable for Dry and Damp Locations
- Improved Lamp Durability with Shatterproof Coated Glass, designed to pass drop tests of 6' on hard surface
- NSF Listed: NSF/ANSI Standard 2 Food Equipment, Splash Zone (Not for Direct Food Zone without additional fixture considerations)

### **OPERATING SPECIFICATIONS**

### **ELECTRICAL AND PERFORMANCE CHARACTERISTICS**


			Bare Lamp	Nominal Lamp	System Wattage*			Initial Lumens*			Visisble Light	Nominal Bare Lamp	Power	Max.
Input Voltage	CRI	Wattage	Lumens	0.78BF	0.88BF	1.18BF	0.78BF	0.88BF	1.18BF	Area	Efficacy	Factor	THD	
	Ballast Dependent	>80	15W	2100 lm	15.8W	17.5W	24.1W	1920 lm	2140 lm	2770 lm	325°	140	>0.9	20%

<sup>\*</sup> Nominal values. Actual values may vary depending on electronic ballast used.


### **RATED LIFE**



# SPECTRAL DISTRIBUTION



# POLAR CANDELA DISTRIBUTION



Maximum Candela = 1248.55 Located at Horizontal Angle = 0, Vertical Angle 0

- 1. Violet Vertical Plane through Horizontal Angles (90-270)
- 2. Green Vertical Plane through Horizontal Angles (0-180)

Beam Angle: 220°

Visible Light Area: 325°

Keystone Technologies • 1390 Welsh Road, North Wales, PA 19454 • Phone (800) 464-2680 • Fax (888) 966-0556 • www.keystonetech.com





# KT-LED15T8-48GC-835-S


T8 LED LAMP

## **WIRING**

**Plug and Play:** Simply replace the existing fluorescent lamp with Keystone Smart Drive LED lamp. No changes to the existing fluorescent ballast wiring needed. For ballast compability questions, please contact Keystone.

## PHYSICAL CHARACTERISTICS

## LAMP DIMENSIONS



NOMINAL LENGTH: 48" BASE TYPE: G13 (Medium Bi-Pin)

#### ORDERING INFORMATION

ORDER CODE	PACKAGING STYLE	PACK QTY.	ITEM STATUS
KT-LED15T8-48GC-835-S-CP	Carton Pack (Egg Crate Packaging)	25	Quick Ship
KT-LED15T8-48GC-835-S-DP	Distributor Pack (Individual Cartons)	20	Quick Ship

## **CATALOG NUMBER BREAKDOWN**

