


Product Number: 75341

Order Abbreviation: LED15T8/L48/DIM/841/SUB/G7

General Description: 4ft SubstiTUBE LED T8, frosted glass, 15W, 82CRI, 2200 Lumen, 4100K, 60000 life



Product Information

Life Time (L70)	50000
Dimming	Yes
Abbrev. With Packaging Info.	LED15T8L48DIM841SUBG7 25/CS 25/SKU
Average Rated Life (hr)	60000
Base	G13
Bulb	T8
Family Brand Name	SubstiTUBE
Color Temperature/CCT (K)	4100
Color Rendering Index (CRI)	82
Lumens	2200
Approx. Lumens	2200
Nominal Voltage (V)	120.00
Nominal Wattage (W)	15.00
Language Strategy	ENGLISH/FRENCH/SPANISH
Ordering Abbreviation	LED15T8/L48/DIM/841/SUB/G7
UPC Code	UPC046135753411
Lamp Finish	Frosted