



A19 REPLACEMENT : E26 & GU24 BASE

DESCRIPTION

LED A-Line Replacement Lamps directly replace incandescent A lamps at a fraction of the energy cost.

FEATURES

- Direct replacement for 40W, 60W, 75W, or 100W incandescent A-lamps
- 240° beam angle is ideal for table lamps, wall sconces, and luminous globe fixtures
- 80% more efficient and 30x longer life than standard incandescent
- Shatter-resistant plastic housing for reduced risk of injury and breakage
- Dimmable models compatible with a wide array of dimmers
- ANSI construction compliant
- Not for use with electronic timers, photocells, or motion/occupancy sensors

WARRANTY

- 5 year limited warranty; see eiko.com for warranty details

APPLICATIONS

- Restaurants & Hospitality
- Retail
- Residential
- Accent/Display Lighting
- Healthcare



A19 E26



A19 GU24



PERFORMANCE	Power Consumption	6W	9W	11W	15W
	Lumens	480	800	1,100	1,600
	Efficacy (LPW)	80	88.9	100	106.7
	CRI	80+			
	Beam	240°			
	CCT	2700K/3000K/4000K/5000K			
	Life (L70)				
ELECTRICAL	Power Factor	>0.7			
	Input Voltage	120V			
CONSTRUCTION	Operating Temperature	-4°F to 104°F (-20°C to 40°C)			
	Base	E26/GU24			
LISTINGS	Certification(s)	cULus Classified			
	Material Usage	RoHS Compliant; no mercury or lead			
	Environment	Suitable for damp locations; Enclosed fixture rated			

PERFORMANCE SUMMARY

A19 MEDIUM BASE (E26):

Order Code	Item #	Lumens	Watts	LPW	CCT	CRI	Beam	MOL	MOD	Life/Hours	Replaces Incan.
10559	LED6WA19/OMN/827-DIM-A	480	6W	80	2700K	80+	240°	4.25"	2.36"	25,000	40W A19
10560	LED6WA19/OMN/830-DIM-A	480	6W	80	3000K	80+	240°	4.25"	2.36"	25,000	40W A19
10561	LED6WA19/OMN/840-DIM-A	480	6W	80	4000K	80+	240°	4.25"	2.36"	25,000	40W A19
10562	LED9WA19/OMN/827-A	800	9W	88.9	2700K	80+	240°	4.25"	2.36"	25,000	60W A19
10563	LED9WA19/OMN/830-A	800	9W	88.9	3000K	80+	240°	4.25"	2.36"	25,000	60W A19
10564	LED9WA19/OMN/840-A	800	9W	88.9	4000K	80+	240°	4.25"	2.36"	25,000	60W A19
10565	LED9WA19/OMN/850-A	800	9W	88.9	5000K	80+	240°	4.25"	2.36"	25,000	60W A19
10566	LED9WA19/OMN/827-DIM-A	800	9W	88.9	2700K	80+	240°	4.25"	2.36"	25,000	60W A19
10567	LED9WA19/OMN/830-DIM-A	800	9W	88.9	3000K	80+	240°	4.25"	2.36"	25,000	60W A19
10569	LED9WA19/OMN/840-DIM-A	800	9W	88.9	4000K	80+	240°	4.25"	2.36"	25,000	60W A19
10574	LED9WA19/OMN/850-DIM-A	800	9W	88.9	5000K	80+	240°	4.25"	2.36"	25,000	60W A19
10581	LED11WA19/OMN/827-DIM-A	1,100	11W	100	2700K	80+	240°	4.25"	2.36"	25,000	75W A19
10583	LED11WA19/OMN/830-DIM-A	1,100	11W	100	3000K	80+	240°	4.25"	2.36"	25,000	75W A19
10584	LED11WA19/OMN/840-DIM-A	1,100	11W	100	4000K	80+	240°	4.25"	2.36"	25,000	75W A19
10586	LED11WA19/OMN/850-DIM-A	1,100	11W	100	5000K	80+	240°	4.25"	2.36"	25,000	75W A19
10598	LED15WA19/OMN/827-DIM-A	1,600	15W	106.7	2700K	80+	240°	4.6"	2.36"	25,000	100W A19
10600	LED15WA19/OMN/830-DIM-A	1,600	15W	106.7	3000K	80+	240°	4.6"	2.36"	25,000	100W A19
10601	LED15WA19/OMN/840-DIM-A	1,600	15W	106.7	4000K	80+	240°	4.6"	2.36"	25,000	100W A19
10603	LED15WA19/OMN/850-DIM-A	1,600	15W	106.7	5000K	80+	240°	4.6"	2.36"	25,000	100W A19

A19 GU24 BASE:

Order Code	Item #	Lumens	Watts	LPW	CCT	CRI	Beam	MOL	MOD	Life/Hours	Replaces Incan.
10575	LED9WA19/OMN/827-GU24-DIM-A	800	9W	88.9	2700K	80+	240°	4.25"	2.36"	25,000	60W A19
10577	LED9WA19/OMN/830-GU24-DIM-A	800	9W	88.9	3000K	80+	240°	4.25"	2.36"	25,000	60W A19
10578	LED9WA19/OMN/840-GU24-DIM-A	800	9W	88.9	4000K	80+	240°	4.25"	2.36"	25,000	60W A19
10589	LED11WA19/OMN/827-GU24-DIM-A	1,100	11W	100	2700K	80+	240°	4.25"	2.36"	25,000	75W A19
10591	LED11WA19/OMN/830-GU24-DIM-A	1,100	11W	100	3000K	80+	240°	4.25"	2.36"	25,000	75W A19
10594	LED11WA19/OMN/840-GU24-DIM-A	1,100	11W	100	4000K	80+	240°	4.25"	2.36"	25,000	75W A19

NOTE: Use order code when ordering.

DIMENSIONS

