


Product Number: 75502

Order Abbreviation: LED17T8/L48/FG/841/SUB/G7

General Description: 4ft SubstiTUBE LED T8, frosted glass, 17W, 82 CRI, 2200 lumens, 4100K, 36000 hours life



Product Information

| | |
|------------------------------|----------------------------------|
| Life Time (L70) | 36000 |
| Abbrev. With Packaging Info. | LED17T8L48FG841SUBG7 10/CS 1/SKU |
| Average Rated Life (hr) | 36000 |
| Bulb | T8 |
| Family Brand Name | SubstiTUBE |
| Color Temperature/CCT (K) | 4100 |
| Color Rendering Index (CRI) | 82 |
| Lumens | 2200 |
| Approx. Lumens | 2200 |
| Nominal Voltage (V) | 120.00 |
| Nominal Wattage (W) | 17.00 |
| Language Strategy | ENGLISH/FRENCH/SPANISH |
| Ordering Abbreviation | LED17T8/L48/FG/841/SUB/G7 |
| UPC Code | UPC046135755026 |