


Product Number: 75503

Order Abbreviation: LED17T8/L48/FG/850/SUB/G7

General Description: 4ft SubstiTUBE LED T8, frosted glass, 17W, 82 CRI, 2200 lumens, 5000K, 36000 hours life




Product Information

Life Time (L70)	36000
Abbrev. With Packaging Info.	LED17T8L48FG850SUBG7 10/CS 1/SKU
Average Rated Life (hr)	36000
Bulb	T8
Family Brand Name	SubstiTUBE
Color Temperature/CCT (K)	5000
Color Rendering Index (CRI)	82
Lumens	2200
Approx. Lumens	2200
Nominal Voltage (V)	120.00
Nominal Wattage (W)	17.00
Language Strategy	ENGLISH/FRENCH/SPANISH
Ordering Abbreviation	LED17T8/L48/FG/850/SUB/G7
UPC Code	UPC046135755033

Product Number: 75503

Order Abbreviation: LED17T8/L48/FG/850/SUB/G7

General Description: 4ft SubstiTUBE LED T8, frosted glass, 17W, 82 CRI, 2200 lumens, 5000K, 36000 hours life



Product Information

Life Time (L70)	36000
Abbrev. With Packaging Info.	LED17T8L48FG850SUBG7 10/CS 1/SKU
Average Rated Life (hr)	36000
Bulb	T8
Family Brand Name	SubstiTUBE
Color Temperature/CCT (K)	5000
Color Rendering Index (CRI)	82
Lumens	2200
Approx. Lumens	2200
Nominal Voltage (V)	120.00
Nominal Wattage (W)	17.00
Language Strategy	ENGLISH/FRENCH/SPANISH
Ordering Abbreviation	LED17T8/L48/FG/850/SUB/G7
UPC Code	UPC046135755033