



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

10440 Airline Highway
70816-0000, LA Baton Rouge
Phone: 225-292-7746
Fax: 225-292-7840



LED18D380W384025 18W Led PAR38 40K Wet Loc 25 Deg

Ge By Current Lamps

Catalog Number	LED18D380W384025
Manufacturer	Ge By Current Lamps
Description	Led PAR38 Lamp, 25 ° Beam Angle, 81, 4000 K, 1700 LM Brightness (Lumens), 18 W, 120 V, White, 25000 H Average Life, E26 Medium Base, Dimmable, 5.31 In Length
Weight per unit	0.7500 (lbs/each)
Product Category	Led Parabolic Reflector Par SH

Features

average life	25000
Base	Medium Screw
lumens	1700

Material, Color, and Finish

Color	White
Color Rendering Index	81

Dimensions and Weight

Overall Length	5.31
----------------	------

Descriptions

Description	18W LED PAR38 40K WET LOC 25 DEG
extra long description	GEL LED18D38OW384025 93171 Directio

Manufacturer Information

Brand	GE Current
GTIN	00043168931717
Manufacturers Part Number	LED18D38OW384025
UPC	043168931717

Taxonomies, Classifications, and Categories

Category Description	LED PAR SHAPE LAMPS
----------------------	---------------------

Packaging

Carton	1
Package	6
Weight Per each	0.75