




GE  
Lighting

### 90160 - GE LED PAR38

LED18DP38W830/40

 Energy-efficient LED lamps. Long life.

### Product Photo



### GENERAL CHARACTERISTICS

|                     |                               |
|---------------------|-------------------------------|
| Lamp Type           | LED-PAR                       |
| Primary Application | Indoor and outdoor Floodlight |
| Rated Life (Hours)  | 25000 h                       |
| Bulb Shape          | PAR38                         |

### PHOTOMETRIC CHARACTERISTICS

|                                |         |
|--------------------------------|---------|
| Center Beam Candle Pwr Candela | 2400 cd |
| Lumens per Watt (Efficacy)     | 72.2 lm |
| Nominal Initial Lumen per Watt | 72      |
| Rated Beam Spread              | 40 rad  |
| Initial Lumens-nominal         | 1300 lm |
| Color Rendering Index-CRI      | 84      |
| Color Temperature              | 3000 K  |

### PRODUCT INFORMATION

|                             |                  |
|-----------------------------|------------------|
| Product Code                | 90160            |
| Description                 | LED18DP38W830/40 |
| Alternative Unit Of Measure | CASE             |

### ELECTRICAL CHARACTERISTICS

|                     |       |
|---------------------|-------|
| Voltage <Nom>       | 120 V |
| Rated power (Watts) | 18 W  |