




KT-LED18T8-48G-850-D

T8 LED LAMP

DESCRIPTION

18W T8 LED | 5000K | >83 CRI | High Efficiency





- Replacement for Conventional Fluorescent Lamp
- Was listed on DLC QPL prior to April 2017
- 50,000+ Hour Lifetime
- Approximately 40% More Energy Efficient that Standard F32T8 Lamps
- Environmentally Friendly: No Mercury Used
- Instant Startup











- Frosted Lens Eliminates Pixelation
- UL Classified
- Operating Temperature: -20°C/-4°F to 45°C/113°F
- Integral Driver (Isolated), Eliminates the Need for External Driver or Ballast
- 100+ Lumens per Watt

OPERATING SPECIFICATIONS

ELECTRICAL CHARACTERISTICS


Input Voltage	Power Consumption	Power Factor	Input Current
120-277Vac	18W	>0.9	0.15A @ 120V 0.07A @ 277V

RATED LIFE


L70 (Hours)	50.000

PHOTOMETRIC CHARACTERISTICS

Color Temperature (CCT)	5000K	
Luminous Flux	2000 lm	
Color Rendering Index (CRI)	>83	
Efficacy	111 lm/W	
Beam Angle	240°	
LED Quantity	120	



POLAR CANDELA DISTRIBUTION



Maximum Candela = 1248.55 Located at Horizontal Angle = 0, Vertical Angle 0

- 1. Violet Vertical Plane through Horizontal Angles (90-270)
- 2. Green Vertical Plane through Horizontal Angles (0-180)

Keystone Technologies • 208 Progress Drive, Montgomeryville, PA 18936 • Phone (800) 464-2680 • Fax (888) 966-0556 • www.keystonelamp.com






KT-LED18T8-48G-850-D

T8 LED LAMP


WIRING DIAGRAMS


1. Cut all existing connections to ballast as shown below and remove ballast.

Typical Ballast Configurations:



2. Re-wire fixture as shown below.





CAUTION, Use only


CAUTION: Use only non-shunted lampholders.

Do not install product in a fixture with shunted lampholders (found in all fixtures using instant start ballasts). If the current lampholders are shunted, remove them and replace them with non-shunted lampholders. Make new connections directly to terminals as indicated above.

Keystone can provide any style replacement lampholders. Call us at 800-464-2680.

PHYSICAL CHARACTERISTICS

LAMP DIMENSIONS



NOMINAL LENGTH: 48" BASE TYPE: G13 (Medium Bi-Pin)

ORDERING INFORMATION

ORDER CODE	PACKAGING STYLE	PACK QTY.	ITEM STATUS
KT-LED18T8-48G-850-D-CP	Carton Pack (Egg Crate Packaging)	25	Quick Ship
KT-LED18T8-48G-850-D-DP	Distributor Pack (Individual Cartons)	12	Quick Ship

CATALOG NUMBER BREAKDOWN

