



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED18T8U6GC850D 18W Led T8 U-Bend 6" 50K Line Voltage *Keystone Technologies*

Catalog Number	LED18T8U6GC850D
Manufacturer	Keystone Technologies
Description	Linear Fluorescent U-Bend Led Lamp, U-Bend, Instant Start Type; 22.25 Inch; UI (Canada and Us), UI, NSF/Ansi, DLC Approval; Food Equipment, Dry and Damp Location Application; 120 to 277 Volt Voltage Rating; 1 Inch Diameter; 18 Watt Wattage; Led Tube
Weight per unit	0.5100 (lbs/each)
Product Category	Shape & Circular Lamps

Features

Beam Spread Angle	220 Degree
Glass Finish	FROSTED
Intensity	2200 Lumen
Item	LED Tube
Voltage Rating	120 to 277 Volt
Wattage	18 Watt

Material, Color, and Finish

Base Type	G13 Medium 2-Pin
Color Rendering Index	80 A
Color Temperature in Kelvin	5000

Dimensions and Weight

Diameter	1 INCH
Length	22.25 Inch



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Additional Information	RoHS Compliant; Shatter Proof Coated Glass; U-Bend Size 6 Inch; Efficacy 122 Lumen per Watt; Visible Light Area 325 Degree; Temperature -4 to 113 Deg F
Commodity Description	Led Linear Fluorescent Straight, U-Shape & Circular Lamps
Description	18W LED T8 U-BEND 6" 50K LINE VOLTAGE
extra long description	U-BEND, INSTANT START TYPE; 22.25 INCH; UL (CANADA AND US), UL, NSF/ANSI, DLC APPROVAL; FOOD EQUIPMENT, DRY AND DAMP LOCATION APPLICATION; 120 TO 277 VOLT VOLTAGE RATING; 1 INCH DIAMETER; 18 WATT WATTAGE; LED TUBE; G13 MEDIUM 2-PIN BASE TYPE; 50000 LIFE IN HOUR; T8 SHAPE DESIGNATION; 2200 LUMEN INTENSITY; 5000; 80 COLOR RENDERING INDEX; FROSTED GLASS FINISH; 220 DEGREE BEAM SPREAD ANGLE; DIRECTDRIVE BRAND; ROHS COMPLIANT; SHATTER PROOF COATED GLASS; U-BEND SIZE 6 INCH; EFFICACY 122 LUMEN PER WATT; VISIBLE
Long Description	LINEAR FLUORESCENT U-BEND LED LAMP, U-BEND, INSTANT START TYPE; 22.25 INCH; UL (CANADA AND US), UL, NSF/ANSI, DLC APPROVAL; FOOD EQUIPMENT, DRY AND DAMP LOCATION APPLICATION; 120 TO 277 VOLT VOLTAGE RATING; 1 INCH DIAMETER; 18 WATT WATTAGE; LED TUBE
Product Type	Linear Fluorescent U-Bend Led Lamp

Manufacturer Information

Brand	Keystone Technologies
GTIN	00890949012536
Manufacturers Part Number	KT-LED18T8-U6GC-850-D
Model	800
UPC	890949012536

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
Type	U-Bend, Instant Start

Packaging

Carton	1
Package	12
Weight Per each	0.51

Uses, Certifications, and Standards

Application	Food Equipment, Dry and Damp Location
Approval	UL (Canada and US), UL, NSF/ANSI, DLC