




ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3706 Frankston Hwy
75701-0000, TX Tyler
Phone: 903-509-9882
Fax: 903-509-9832



LED26T860P2S865D 5' 26W Led Signhero 65K 360DEG BLST Bypass *Keystone Technologies*

Catalog Number	LED26T860P2S865D
Manufacturer	Keystone Technologies
Description	5 FT. Led Sign Tube, 6500K, Double Sided Output and Rotatable R17D End Caps, 26W, 120-277V Input
Weight per unit	1.3 (lbs/each)
Product Category	Led Specialty Lamps & Modules

Features

Ballast Type	N/A
beam angle	360
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
Lamp Type	T8
lumens	3250
Nominal Length	60 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	26
Wire Type	N/A

Material, Color, and Finish

Base Type	R17D
color rendering index (cri)	>80 Deg
color temperature	6500
housing color	N/A

Descriptions

Description	5' 26W LED SIGNHERO 65K 360DEG BLST BYPASS
extra long description	Key KT-LED26T8-60P2S-865-D /G2 5 ft
Long Description	5 FT. LED SIGN TUBE, 6500K, DOUBLE SIDED OUTPUT AND ROTATABLE R17D END CAPS, 26W, 120-277V INPUT
Product Type	5 FT. Led Sign Tube, 6500K, Double Sided Output and Rotatable

Manufacturer Information

Brand	Keystone
GTIN	00843654132266
Manufacturers Part Number	KT-LED26T8-60P2S-865-D /G2
UPC	843654132266



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3706 Frankston Hwy
75701-0000, TX Tyler
Phone: 903-509-9882
Fax: 903-509-9832

Taxonomies, Classifications, and Categories

Category Description LED SPECIALTY LAMPS & MODULES

Packaging

Carton 1

Package 9

Weight Per each 1.28

Uses, Certifications, and Standards

Energy Star N