



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3448 Sherwood Way
76901-0000, TX San Angelo
Phone: 325-944-7321
Fax: 325-944-1579



LED4.5B10BENTDI *Delisted* 4.5W Led B10 Bent/Flame Tip Fil 27K

Sylvania-Ledvance

| | |
|------------------|--|
| Catalog Number | LED4.5B10BENTDI |
| Manufacturer | Sylvania-Ledvance |
| Description | OBS79763 B10, 4.5W Dimmable, 80CRI, 400 Lumen, 2700K, 15000 Life |
| Weight per unit | 0.1110 (lbs/each) |
| Product Category | Led Specialty Lamps & Modules |

Features

| | |
|----------------|------------|
| average life | 15000 |
| Base | E26 Medium |
| Lamp Type | LED B10 |
| lumens | 400 |
| Shape | B10 |
| Voltage | 120.00 V |
| Voltage Rating | 120.00 |
| Wattage | 4.50 |

Material, Color, and Finish

| | |
|-----------------------------|---------|
| color rendering index (cri) | 80 |
| Style | B-shape |

Dimensions and Weight

| | |
|------|------|
| Size | 1.38 |
|------|------|

Descriptions

| | |
|------------------------|--|
| Description | *DELISTED* 4.5W LED B10 BENT/FLAME TIP FIL 27K |
| extra long description | SYL LED4.5B10BENTDIM827FILG2BL2/797 |
| Long Description | OBS79763 B10, 4.5W Dimmable, 80CRI, 400 Lumen, 2700K, 15000 life |
| Product Type | LED4.5B10BENTDIM827FILG2BL2 12/CS 2/Sku |

Manufacturer Information

| | |
|---------------------------|--------------------------------|
| Brand | SYLVANIA |
| GTIN | 00046135797637 |
| Manufacturers Part Number | LED4.5B10BENTDIM827FILG2BL2/79 |
| UPC | 046135797637 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LED DECORATIVE C, CA, F, G SHAPE LAMPS |
|----------------------|--|

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 12 |
| Weight Per each | 0.111 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3448 Sherwood Way
76901-0000, TX San Angelo
Phone: 325-944-7321
Fax: 325-944-1579

Uses, Certifications, and Standards

standard

cULus
