



KT-LED43T8-96GC-850-D

T8 LED LAMP

DESCRIPTION

43W T8 LED | 5000K | >80 CRI | High Efficiency | 8 Foot









LAMP TYPE: Linear	COLOR TEMPERATURE: 5000K
BULB TYPE: T8 LED	COLOR RENDERING INDEX (CRI): >80
BASE TYPE: Fa8 (Single-Pin)	WARRANTY: 5 Years
WATTAGF: 43W	

PRODUCT FEATURES

- Replacement for Conventional T8/T12 8 Foot Single-Pin Fluorescent Lamp
- Double Ended Line Voltage Wiring: Connect power to each end for simplified installation
- 50,000+ Hour Lifetime
- Approximately 50% More Energy Efficient then Standard F96T12 Lamps
- Environmentally Friendly: No Mercury Used
- Instant Startup
- Includes 2 C-clips to be installed with the lamps into the fixture ballast cover to prevent any potential un-desired lamp twisting or sagging
- Frosted Lens Elimates Pixelation
- UL Classified
- Operating Temperature: -20°C/-4°F to 55°C/131°F

- Integral Driver (Isolated), Eliminates the Need for External Driver or Ballast
- 120+ Lumens per Watt
- Improved Lamp Durability with Shatterproof Coated Glass, designed to pass drop tests of 6' on hard surface
- NSF Listed: NSF/ANSI Standard 2 -Food Equipment, Splash Zone (Not for Direct Food Zone without additional fixture considerations)

OPERATING SPECIFICATIONS

ELECTRICAL CHARACTERISTICS

Input Voltage	Power Consumption	Power Factor	Input Current
120-277Vac	43W	>0.9	0.36 @ 120V 0.16 @ 277V


PHOTOMETRIC CHARACTERISTICS

Color Temperature	5000K
Luminous Flux	5550 lm
Color Rendering Index (CRI)	>80
Efficacy	129 lm/W
Beam Angle	325°

RATED LIFE

L70 (Hours)	50,000
-------------	--------


POLAR CANDELA DISTRIBUTION



Located at Horizontal Angle = 0, Vertical Angle 0

1.Violet Vertical Plane through Horizontal Angles (90-270)

2. Green Vertical Plane through Horizontal Angles (0-180)







KT-LED43T8-96GC-850-D


T8 LED LAMP


WIRING DIAGRAMS

1. Identify ballast configuration as shown below and cut all wires connected to the ballast accordingly.

Typical Ballast Configurations:


BALLAST BLUE WHITE (NEUTRAL) ELECTRONIC LAMP BALLAST BLUE BLUE







- 2. Confirm that the lampholders in the fixture are single-pin Fa8 lampholders. These DirectDrive LED tubes require single-pin Fa8 lampholders.
- 3. Rewire the fixture using existing lampholders as shown below according to the original ballast wiring configuration.

Typical Ballast Configurations:








PHYSICAL CHARACTERISTICS

LAMP DIMENSIONS



A (Illuminated Length)	91.5"	
B (Body Length)	93.31"	
C (Cross Section: Width x Height)	1.08" x 1.31"	

NOMINAL LENGTH: 96" **BASE TYPE:** Fa8 (Single-Pin)

ORDERING INFORMATION

ORDER CODE	PACKAGING STYLE	PACK QTY.	ITEM STATUS
KT-LED43T8-96GC-850-D-CP	Distributor Pack (Individual Cartons)	10	Quick Ship

CATALOG NUMBER BREAKDOWN

