

KT-LED6A19-0-8XX-ND

REPLACEMENT LAMP

DESCRIPTION

6W A19 Lamp | 2700–5000K | >80 CRI | Omni-Directional



RoHS
Compliant

2YEAR
WARRANTY

LAMP TYPE: A19
BASE TYPE: E26 (Medium)
WATTAGE: 6W
COLOR TEMPERATURE: 2700–5000K
COLOR RENDERING INDEX (CRI): >80
WARRANTY: 2 Years
RATED LIFE: L70 (15,000 Hours)



TYPICAL APPLICATIONS

- Table, Desk, and Floor Lamps
- Wall Sconces
- Surface Mount Ceiling Fixtures
- General Lighting
- Pendant Lights

PRODUCT FEATURES


- Energy Efficient, 80%+ Energy Savings over Legacy Equivalents
- Lower Heat Generation than Legacy Equivalents
- PF >0.60
- Complies with Part 15 of FCC
- Durable Plastic housing lowers the risk for breakage
- UL enclosed rated, suitable for use in totally enclosed luminaires
- Energy Star Enclosed Fixture Rated
- Operating temperature range –4°F/–20°C to 95°F/35°C
- Long Life minimizes replacement and maintenance costs
- Meets Energy Star requirements
- UL Listed
- Smooth diffused lens for comfortable glare free performance
- ANSI complaint construction ensures fitment for intended applications

ELECTRICAL AND PERFORMANCE SPECIFICATIONS

Keystone Catalog Number	Description	Color Temp	Input Voltage	Rated Lamp Wattage	Legacy Equivalent Wattage	Base Type	Lumens	CRI	Light Distribution	Dimmable	Efficacy
KT-LED6A19-0-827-ND	A19 bulb. Omni-Directional, non-dimming	2700K	120V	6W	40W halogen	E26	480	>80	230°	No	80 lm/W
KT-LED6A19-0-830-ND	A19 bulb. Omni-Directional, non-dimming	3000K	120V	6W	40W halogen	E26	480	>80	230°	No	80 lm/W
KT-LED6A19-0-850-ND	A19 bulb. Omni-Directional, non-dimming	5000K	120V	6W	40W halogen	E26	480	>80	230°	No	80 lm/W

KT-LED6A19-0-8XX-ND
REPLACEMENT LAMP

PHYSICAL CHARACTERISTICS



PACKAGING

Carton Quantity	60 pcs
Carton Dimensions	15.55" × 13.07" × 10"
Carton Weight	9.7 lbs

LAMP DIMENSIONS

A (Length)	4.33"
B (Diameter)	2.36"

BASE TYPE: E26 (Medium)

ORDERING INFORMATION

ORDER CODE	CARTON QUANTITY	ITEM STATUS
KT-LED6A19-0-8XX-ND	60 pcs	Active

CATALOG NUMBER BREAKDOWN

KT-LED6A19-0-8XX-ND

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8

- 1 Keystone Technologies
- 2 LED Lamp
- 3 Wattage
- 4 Lamp Shape
- 5 Omni-Directional
- 6 800 Series
- 7 Color Temperature
- 8 Non-Dimming