



### Description:


- 11 Watts Replaces up to 26w HID Lamps
- 360° Omni-Directional Beam Angle
- 120-277V UL 1993, UL1598C US and Canada
- 120-347V UL 1993, UL1598C Canada only
- UL damp environments (USA & Can)
- G24q 4 Pin base
- >25,000 rated LED life
- 5 year limited warranty (see website for details)
- Compatible with 13/18/26W Electronic Ballast or 120-277VAC Line Voltage




### Photometric Data

Technical Specifications		
Models US/CAN	LED-7320-27A	LED-7320-40A
CCT	2700K	4000K
Power Consumption	9 watts	
Replaces	26w	
Mounting	G24q	
Voltage	120-277V	
LED Type		
Beam Angle	360°	
Dimmable	No	
Operating Temp	-40°F - +122°F	
Rated R70 Life	>25,000 Hrs.	
Warranty	5 Year Limited*	
LM79 Specifications	Yes	Yes
Power (W)	11w	11w
CCT	2635	3977
Lumen Output	850 lm	900 lm
Efficacy		
THD @ 277V		
PF @ 277V	0.88	0.88
CRI:	85.4	84.9
R9		
Duv		
Test Data Source	IES LM79-08 NVLAP 200707-0	
Packaging		
Unit	6.2" X 1.4"	
Master		

### Lux Distance Curve



### Polar Curves



### ISO Illuminance Diagram

**\*Compatible Ballasts:**

- Philips Advance ICF-2S26-H1-LD
- Philips Advance ICF-2S42-M2-LD
- Philips Advance ICF-2S18-HA-LD
- Philips Advance REB-2S13-M6-EL
- Hatch HC213PS/UV/D
- Hatch HC218PS/UV/D
- Triad C213UNVME
- Triad QTP 2x26DF/UNV DM
- Pony NPY-120-126-BLS
- Fulham Workhorse2 WH2-277-L
- Fulham Workhorse2 WH2-120-L

Note: Other electronic ballast most likely compatible as well

