Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

201 South Persimmon Street
77375-6855, TX Tomball
Phone: 281-357-5300
Fax: 281-357-5005



LED7DAV3827W 7W Led A19 Dim 27K

Ge By Current Lamps

Catalog Number	LED7DAV3827W
Manufacturer	Ge By Current Lamps
Description	A19 Led Lamp, 120 ° Beam Angle, 80, 2700 K, 470 LM Brightness (Lumens), 7 W, 120 V, White, Glass Material, 25000 H Average Life, E26 Medium Screw-In Base, Dimmable, 4.63 In Length
Weight per unit	0.5300 (lbs/each)
Product Category	Led A-Line A Shape Lamps

Features

lumens	470
Voltage Rating	120

Dimensions and Weight

Size	117.5

Descriptions

Description	7W LED A19 DIM 27K
Special Features	Color Rendering Index (CRI) 78.0, 62.0IN Bulb Diameter

Manufacturer Information

Brand	GE Current
GTIN	00043168140638
Manufacturers Part Number	LED7DAV3/827/W
UPC	043168140638

Taxonomies, Classifications, and Categories

Category Description	LED A-LINE SHAPE LAMPS
Type	LEDs_Replacement Lamps_A-line_A-Line Dimming

Availability

Manufacturer Status	Inactive
Status	Inactive

Packaging

Carton	1
Package	6
Weight Per each	0.53