

69921 - LED7DMR16D830/35

GE LED MR16 Gen 2

• Energy-efficient LED lamps. Long life.









GENERAL CHARACTERISTICS

Lamp Type Replacement Lamps -

Directional Bulb MR16

Base 2-Pin (GU5.3)
Bulb Shape MR16
Color Silver

Dimming Capability Operates on dimming circuits.

See GELighting.com/dimming

for further information

Equivalent Wattage (NOM) 35.0 W
Lamp Type LED-MR
Life in Years (NOM) 22.8
Rated Life (NOM) 25000.0 h

PHOTOMETRIC CHARACTERISTICS

Beam Spread (NOM) 35.0 ° Center Beam Candlepower 1100.0

(CBCP) (NOM)

Color Rendering Index 83.0

(CRI) (NOM)

Color Temperature (NOM) 3000.0 K Initial Lumens (NOM) 390.0 Lumens per Watt (Efficacy) 56.0 Im

(NOM)

Nominal Initial Lumens per 55.7

Watt (NOM)

ELECTRICAL CHARACTERISTICS

Estimated Energy Cost per 0.84

Year (NOM)

Voltage (NOM) 12.0 Wattage (NOM) 7.0

DIMENSIONS

Bulb Diameter (DIA) (NOM) 2.000 in(50.8 mm)
Maximum Overall Length 1.880 in(47.8 mm)

(MOL) (NOM)

PRODUCT INFORMATION

Product Code 69921

Description LED7DMR16D830/35

Standard Package Case

Standard Package GTIN 10043168699218 Standard Package Quantity 6

Standard Package Quantity 6
Sales Unit Unit
No Of Items Per Sales Unit 6
No Of Items Per Standard 6

Package

UPC 043168699211