



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LED7T818GC850D 7W Led T8 18" 50K *Keystone Technologies*

Catalog Number	LED7T818GC850D
Manufacturer	Keystone Technologies
Description	7W Led T8 Tube, Shatter-Proof Coated Glass, Internal Driver, 18", 5000K, 120-277V Input, 25 PCS Cartons, Individually Sleeved
Weight per unit	0.3200 (lbs/each)
Product Category	Shape & Circular Lamps

### Features

Ballast Type	N/A
beam angle	240
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
Lamp Type	T8
lumens	750
Nominal Length	18 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	7
Wire Type	N/A

### Material, Color, and Finish

Base Type	G13
color rendering index (cri)	>80 Deg
color temperature	5000
housing color	N/A

### Descriptions

Construction	Frosted Shatterproof Glass
Description	7W LED T8 18" 50K
extra long description	Key KT-LED7T8-18GC-850-D-CP 7W LED
Long Description	7W LED T8 Tube, Shatter-Proof Coated Glass, Internal Driver, 18", 5000K, 120-277V Input, 25 pcs cartons, Individually Sleeved
Product Type	7W Led T8 Tube, Shatter-Proof Coated Glass, Internal Driver,



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Keystone
GTIN	00890949009406
Manufacturers Part Number	KT-LED7T8-18GC-850-D-CP
UPC	890949009406

## Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

## Packaging

Carton	25
Weight Per each	0.32

## Uses, Certifications, and Standards

Energy Star	N
-------------	---