



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED7T824GC850D 7W Led T8 24" 50K Single End Line Voltage *Keystone Technologies*

Catalog Number	LED7T824GC850D
Manufacturer	Keystone Technologies
Description	Linear Fluorescent Straight Led Lamp, Linear, Instant Start Type; 23.19 Inch; UI (Canada and Us), UI, NSF/Ansi, Etl, DLC Approval; Food Equipment, Splash Zone Application; 120 to 277 Volt Ac Voltage Rating; 1.1 Inch Diameter
Weight per unit	0.3000 (lbs/each)
Product Category	Shape & Circular Lamps

Features

Beam Spread Angle	240 Degree
Current Rating	0.06 Amp at 120 Volt AC, 0.03 Amp at 277 Volt AC
Glass Finish	FROSTED
Intensity	950 Lumen
Item	LED Lamp
Voltage Rating	120 to 277 Volt AC
Wattage	7 Watt

Material, Color, and Finish

Base Type	G13 Medium 2-Pin
Color Rendering Index	83
Color Temperature in Kelvin	5000

Dimensions and Weight

Diameter	1.1 Inch
Length	23.19 Inch



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Additional Information	RoHS Compliant; Shatter Proof Coated Glass; Efficacy 136 Lumen per Watt; Visible Light Area 325 Degree; Temperature -4 to 113 Deg F
Commodity Description	Led Linear Fluorescent Straight, U-Shape & Circular Lamps
Description	7W LED T8 24" 50K SINGLE END LINE VOLTAGE
extra long description	LINEAR, INSTANT START TYPE; 23.19 INCH; UL (CANADA AND US), UL, NSF/ANSI, ETL, DLC APPROVAL; FOOD EQUIPMENT, SPLASH ZONE APPLICATION; 120 TO 277 VOLT AC VOLTAGE RATING; 1.1 INCH DIAMETER; 0.06 AMP AT 120 VOLT AC, 0.03 AMP AT 277 VOLT AC CURRENT RATING; 7 WATT WATTAGE; LED LAMP; G13 MEDIUM 2-PIN BASE TYPE; 50000 (L70) LIFE IN HOUR; T8 SHAPE DESIGNATION; 950 LUMEN INTENSITY; 5000; 83 COLOR RENDERING INDEX; FROSTED GLASS FINISH; 240 DEGREE BEAM SPREAD ANGLE; DIRECTDRIVE BRAND; ROHS COMPLIANT; SHATTER PROOF CO
Long Description	LINEAR FLUORESCENT STRAIGHT LED LAMP, LINEAR, INSTANT START TYPE; 23.19 INCH; UL (CANADA AND US), UL, NSF/ANSI, ETL, DLC APPROVAL; FOOD EQUIPMENT, SPLASH ZONE APPLICATION; 120 TO 277 VOLT AC VOLTAGE RATING; 1.1 INCH DIAMETER
Product Type	Linear Fluorescent Straight Led Lamp

Manufacturer Information

Brand	Keystone Technologies
GTIN	00890949013212
Manufacturers Part Number	KT-LED7T8-24GC-850-D
Model	800
UPC	890949013212

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
Type	Linear, Instant Start

Packaging

Carton	1
Package	25
Weight Per each	0.3

Uses, Certifications, and Standards

Application	Food Equipment, Splash Zone
Approval	UL (Canada and US), UL, NSF/ANSI, ETL, DLC