



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED82PH840D 8W Led 2PIN CFL 40K Horizontal Ballast Bypass

Keystone Technologies

Catalog Number	LED82PH840D
Manufacturer	Keystone Technologies
Description	Compact Fluorescent Led Lamp, Compact, Instant Start Type; 5.6 Inch; UI (Canada and Us) Approval; 120 to 277 Volt Voltage Rating; 1.22 Inch Diameter; 8 Watt Wattage; Led Lamp; G24D 2-Pin Base Type; 50000 (L70) Life In Hour; 900 Lumen Intensity; 4000
Weight per unit	0.2600 (lbs/each)
Product Category	Integrated Lamps

Features

Beam Spread Angle	120 Degree
Glass Finish	FROSTED
Intensity	900 LUMEN
Item	LED Lamp
Voltage Rating	120 to 277 Volt
Wattage	8 Watt

Material, Color, and Finish

Base Type	G24d 2-Pin
Color Rendering Index	83
Color Temperature in Kelvin	4000

Dimensions and Weight

Diameter	1.22 INCH
Length	5.6 INCH



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Additional Information	RoHS Compliant; System Wattage 8 Watt; Efficacy 113 Lumen per Watt; Temperature -4 to 113 Deg F
Commodity Description	Led Compact Fluorescent Integrated & Non-Integrated Lamps
Description	8W LED 2PIN CFL 40K HORIZONTAL BALLAST BYPASS
extra long description	COMPACT, INSTANT START TYPE; 5.6 INCH; UL (CANADA AND US), UL APPROVAL; DRY AND DAMP LOCATION APPLICATION; 120 TO 277 VOLT VOLTAGE RATING; 1.22 INCH DIAMETER; 8 WATT WATTAGE; LED LAMP; G24D 2-PIN BASE TYPE; 50000 (L70) LIFE IN HOUR; 950 LUMEN INTENSITY; 4000; 83 COLOR RENDERING INDEX; FROSTED GLASS FINISH; HORIZONTAL BURNING POSITION; 120 DEGREE BEAM SPREAD ANGLE; DIRECTDRIVE BRAND; ROHS COMPLIANT; WIDTH 1.61 INCH; EFFICACY 113 LUMEN PER WATT; TEMPERATURE RATING -4 TO 113 DEG F; PACKAGING TYPE DISTRIBUTOR
Long Description	COMPACT FLUORESCENT LED LAMP, COMPACT, INSTANT START TYPE; 5.6 INCH; UL (CANADA AND US) APPROVAL; 120 TO 277 VOLT VOLTAGE RATING; 1.22 INCH DIAMETER; 8 WATT WATTAGE; LED LAMP; G24D 2-PIN BASE TYPE; 50000 (L70) LIFE IN HOUR; 900 LUMEN INTENSITY; 4000
Product Type	Compact Fluorescent Led Lamp

Manufacturer Information

Brand	Keystone Technologies
GTIN	00890949012727
Manufacturers Part Number	KT-LED82P-H-840-D
Model	800
UPC	890949012727

Taxonomies, Classifications, and Categories

Category Description	LED PLUG-IN (REPLACEMENT FOR CFL BIAX LAMPS)
Type	Compact, Instant Start

Packaging

Carton	1
Package	10
Weight Per each	0.26

Uses, Certifications, and Standards

Approval	UL (CANADA AND US)
----------	--------------------