SINCE 1945 KEYSTONE LIGHT MADE EASY®

ESSENTIAL SERIES
GENERAL PURPOSE LED BULBS

KT-LED9.5A19-O-8XX /G2
REPLACEMENT LAMP

DESCRIPTION
9.5W A19 Lamp | 2700–5000K | >80 CRI | Omni-Directional

LAMP TYPE: A19
BASE TYPE: E26 (Medium)
WATTAGE: 9.5W
COLOR TEMPERATURE: 2700–5000K
COLOR RENDERING INDEX (CRI): >80
WARRANTY: 3 Years
RATED LIFE: L70 (15,000 Hours)



TYPICAL APPLICATIONS
- Table, Desk, and Floor Lamps
- Wall Sconces
- Surface Mount Ceiling Fixtures
- General Lighting
- Pendant Lights

PRODUCT FEATURES
- Energy Efficient, 80%+ Energy Savings over Legacy Equivalents
- Lower Heat Generation than Legacy Equivalents
- PF >0.70
- Complies with Part 15 of FCC
- Durable Plastic housing lowers the risk for breakage
- ANSI compliant construction ensures fitment for intended applications
- Rated for open, recessed, and enclosed fixtures
- Operating temperature range –4ºF/–20ºC to 95ºF/35ºC
- Long Life minimizes replacement and maintenance costs
- Meets Energy Star requirements
- UL Listed
- Smooth diffused lens for comfortable glare free performance
- Smooth, uniform dimming
- Suitable for damp locations

ELECTRICAL AND PERFORMANCE SPECIFICATIONS


Keystone Catalog Number	Description	Color Temp	Input Voltage	Rated Lamp Wattage	Legacy Equivalent Wattage	Base Type	Lumens	CRI	Beam Angle	Dimmable	Efficacy
KT-LED9.5A19-O-827 /G2	A19 bulb. Omni-Directional, dimmable	2700K	120V	9.5W	60W	E26	800	>80	230º	Yes	84 lm/W
KT-LED9.5A19-O-830 /G2	A19 bulb. Omni-Directional, dimmable	3000K	120V	9.5W	60W	E26	800	>80	230º	Yes	84 lm/W
KT-LED9.5A19-O-835 /G2	A19 bulb. Omni-Directional, dimmable	3500K	120V	9.5W	60W	E26	800	>80	230º	Yes	84 lm/W
KT-LED9.5A19-O-840 /G2	A19 bulb. Omni-Directional, dimmable	4000K	120V	9.5W	60W	E26	800	>80	230º	Yes	84 lm/W
KT-LED9.5A19-O-850 /G2	A19 bulb. Omni-Directional, dimmable	5000K	120V	9.5W	60W	E26	800	>80	230º	Yes	84 lm/W

KEYSTONE SINCE 1945 LIGHT MADE EASY®

ESSENTIAL SERIES
GENERAL PURPOSE LED BULBS

KT-LED9.5A19-O-8XX /G2
REPLACEMENT LAMP

PHYSICAL CHARACTERISTICS



PACKAGING

Carton Quantity	60 pcs
Carton Dimensions	24.61" × 14.76" × 4.72"
Carton Weight	7.34 lbs

LAMP DIMENSIONS

A (Length)	3.94"
B (Diameter)	2.36"

BASE TYPE: E26 (Medium)

ORDERING INFORMATION

CATALOG NUMBER	CARTON QUANTITY	EASY CODE	UPC
KT-LED9.5A19-O-827 /G2	60 pcs	OSD-58	843654130170
KT-LED9.5A19-O-830 /G2	60 pcs	UDH-32	843654130187
KT-LED9.5A19-O-835 /G2	60 pcs	XUC-27	843654130194
KT-LED9.5A19-O-840 /G2	60 pcs	AHJ-60	843654130200
KT-LED9.5A19-O-850 /G2	60 pcs	RNV-78	843654130217

CATALOG NUMBER BREAKDOWN

KT-LED9.5A19-O-8XX /G2

1 2 3 4 5 6 7 8

1 **Keystone Technologies**
2 **LED Lamp**
3 **Wattage**
4 **Lamp Shape**
5 **Omni-Directional**
6 **800 Series**
7 **Color Temperature**
8 **Generation 2**

SINCE 1945 KEYSTONE LIGHT MADE EASY®

ESSENTIAL SERIES
GENERAL PURPOSE LED BULBS

KT-LED9.5A19-O-8XX /G2
REPLACEMENT LAMP

DESCRIPTION
9.5W A19 Lamp | 2700–5000K | >80 CRI | Omni-Directional

LAMP TYPE: A19
BASE TYPE: E26 (Medium)
WATTAGE: 9.5W
COLOR TEMPERATURE: 2700–5000K
COLOR RENDERING INDEX (CRI): >80
WARRANTY: 3 Years
RATED LIFE: L70 (15,000 Hours)



TYPICAL APPLICATIONS
- Table, Desk, and Floor Lamps
- Wall Sconces
- Surface Mount Ceiling Fixtures
- General Lighting
- Pendant Lights

PRODUCT FEATURES
- Energy Efficient, 80%+ Energy Savings over Legacy Equivalents
- Lower Heat Generation than Legacy Equivalents
- PF >0.70
- Complies with Part 15 of FCC
- Durable Plastic housing lowers the risk for breakage
- ANSI compliant construction ensures fitment for intended applications
- Rated for open, recessed, and enclosed fixtures
- Operating temperature range –4ºF/–20ºC to 95ºF/35ºC
- Long Life minimizes replacement and maintenance costs
- Meets Energy Star requirements
- UL Listed
- Smooth diffused lens for comfortable glare free performance
- Smooth, uniform dimming
- Suitable for damp locations

ELECTRICAL AND PERFORMANCE SPECIFICATIONS


Keystone Catalog Number	Description	Color Temp	Input Voltage	Rated Lamp Wattage	Legacy Equivalent Wattage	Base Type	Lumens	CRI	Beam Angle	Dimmable	Efficacy
KT-LED9.5A19-O-827 /G2	A19 bulb. Omni-Directional, dimmable	2700K	120V	9.5W	60W	E26	800	>80	230º	Yes	84 lm/W
KT-LED9.5A19-O-830 /G2	A19 bulb. Omni-Directional, dimmable	3000K	120V	9.5W	60W	E26	800	>80	230º	Yes	84 lm/W
KT-LED9.5A19-O-835 /G2	A19 bulb. Omni-Directional, dimmable	3500K	120V	9.5W	60W	E26	800	>80	230º	Yes	84 lm/W
KT-LED9.5A19-O-840 /G2	A19 bulb. Omni-Directional, dimmable	4000K	120V	9.5W	60W	E26	800	>80	230º	Yes	84 lm/W
KT-LED9.5A19-O-850 /G2	A19 bulb. Omni-Directional, dimmable	5000K	120V	9.5W	60W	E26	800	>80	230º	Yes	84 lm/W

KEYSTONE SINCE 1945 LIGHT MADE EASY®

ESSENTIAL SERIES
GENERAL PURPOSE LED BULBS

KT-LED9.5A19-O-8XX /G2
REPLACEMENT LAMP

PHYSICAL CHARACTERISTICS



PACKAGING

Carton Quantity	60 pcs
Carton Dimensions	24.61" × 14.76" × 4.72"
Carton Weight	7.34 lbs

LAMP DIMENSIONS

A (Length)	3.94"
B (Diameter)	2.36"

BASE TYPE: E26 (Medium)

ORDERING INFORMATION

CATALOG NUMBER	CARTON QUANTITY	EASY CODE	UPC
KT-LED9.5A19-O-827 /G2	60 pcs	OSD-58	843654130170
KT-LED9.5A19-O-830 /G2	60 pcs	UDH-32	843654130187
KT-LED9.5A19-O-835 /G2	60 pcs	XUC-27	843654130194
KT-LED9.5A19-O-840 /G2	60 pcs	AHJ-60	843654130200
KT-LED9.5A19-O-850 /G2	60 pcs	RNV-78	843654130217

CATALOG NUMBER BREAKDOWN

KT-LED9.5A19-O-8XX /G2

1 2 3 4 5 6 7 8

1 **Keystone Technologies**
2 **LED Lamp**
3 **Wattage**
4 **Lamp Shape**
5 **Omni-Directional**
6 **800 Series**
7 **Color Temperature**
8 **Generation 2**