SINCE 1945
KEYSTONE
LIGHT MADE EASY

ESSENTIAL SERIES
GENERAL PURPOSE LED BULBS

KT-LED9.5A19-O-8XX
REPLACEMENT LAMP

DESCRIPTION
9.5W A19 Lamp | 2700–5000K | >80 CRI | Omni-Directional

c UL us LISTED · RoHS Compliant · TRUSTED NB WARRANTY · 3 YEAR WARRANTY

- **LAMP TYPE:** A19
- **BASE TYPE:** E26 (Medium)
- **WATTAGE:** 9.5W
- **COLOR TEMPERATURE:** 2700–5000K
- **COLOR RENDERING INDEX (CRI):** >80
- **WARRANTY:** 3 Years
- **RATED LIFE:** L70 (15,000 Hours)



TYPICAL APPLICATIONS
- Table, desk, and floor lamps
- Wall sconces
- Surface-mount ceiling fixtures
- General lighting
- Pendant lights

PRODUCT FEATURES
- Energy efficient, 80%+ energy savings over legacy equivalents
- Lower heat generation than legacy equivalents
- Smooth, diffused lens for comfortable glare-free performance
- Durable plastic housing lowers the risk for breakage
- Long life minimizes replacement and maintenance costs
- ANSI compliant construction ensures fitment for intended applications
- Suitable for use in damp locations
- Smooth, uniform dimming
- Operating temperature range −4°F/−20°C to 95°F/35°C
- PF > 0.70
- UL Listed
- Complies with Part 15 of FCC

PERFORMANCE SPECIFICATIONS


Keystone Catalog Number	Base Type	Rated Lamp Wattage	Legacy Equivalent Wattage	Color Temp	Lumens	Efficacy	Input Voltage	CRI	Beam Angle	Dimmable
KT-LED9.5A19-O-827	E26	9.5W	60W halogen	2700K	800	84 lm/W	120V	>80	230°	Yes
KT-LED9.5A19-O-830	E26	9.5W	60W halogen	3000K	800	84 lm/W	120V	>80	230°	Yes
KT-LED9.5A19-O-835	E26	9.5W	60W halogen	3500K	800	84 lm/W	120V	>80	230°	Yes
KT-LED9.5A19-O-840	E26	9.5W	60W halogen	4000K	800	84 lm/W	120V	>80	230°	Yes
KT-LED9.5A19-O-850	E26	9.5W	60W halogen	5000K	800	84 lm/W	120V	>80	230°	Yes

KEYSTONE SINCE 1945 LIGHT MADE EASY

ESSENTIAL SERIES
GENERAL PURPOSE LED BULBS

KT-LED9.5A19-O-8XX
REPLACEMENT LAMP

PHYSICAL SPECIFICATIONS



LAMP DIMENSIONS

A (Diameter)	2.36"
B (Length)	4.33"

BASE TYPE: E26 (Medium)

PACKAGING

Carton Quantity	60 pcs
Carton Dimensions	15.55" × 13.07" × 10"
Carton Weight	9.9 lbs

ORDERING INFORMATION

ORDER CODE	EASY CODE	UPC
KT-LED9.5A19-O-827	HMT-55	843654126418
KT-LED9.5A19-O-830	SEG-00	843654126425
KT-LED9.5A19-O-835	ERP-91	843654127552
KT-LED9.5A19-O-840	GWA-29	843654126432
KT-LED9.5A19-O-850	ICQ-61	843654126449

CATALOG NUMBER BREAKDOWN

KT-LED9.5A19-O-8XX

1 2 3 4 5 6 7

1 Keystone Technologies
2 LED Lamp
3 Wattage
4 Lamp Shape
5 Omni-Directional
6 80 CRI
7 CCT

SINCE 1945
KEYSTONE
LIGHT MADE EASY

ESSENTIAL SERIES
GENERAL PURPOSE LED BULBS

KT-LED9.5A19-O-8XX
REPLACEMENT LAMP

DESCRIPTION
9.5W A19 Lamp | 2700–5000K | >80 CRI | Omni-Directional

c UL us LISTED · RoHS Compliant · TRUSTED NB WARRANTY · 3 YEAR WARRANTY

- **LAMP TYPE:** A19
- **BASE TYPE:** E26 (Medium)
- **WATTAGE:** 9.5W
- **COLOR TEMPERATURE:** 2700–5000K
- **COLOR RENDERING INDEX (CRI):** >80
- **WARRANTY:** 3 Years
- **RATED LIFE:** L70 (15,000 Hours)



TYPICAL APPLICATIONS
- Table, desk, and floor lamps
- Wall sconces
- Surface-mount ceiling fixtures
- General lighting
- Pendant lights

PRODUCT FEATURES
- Energy efficient, 80%+ energy savings over legacy equivalents
- Lower heat generation than legacy equivalents
- Smooth, diffused lens for comfortable glare-free performance
- Durable plastic housing lowers the risk for breakage
- Long life minimizes replacement and maintenance costs
- ANSI compliant construction ensures fitment for intended applications
- Suitable for use in damp locations
- Smooth, uniform dimming
- Operating temperature range −4°F/−20°C to 95°F/35°C
- PF > 0.70
- UL Listed
- Complies with Part 15 of FCC

PERFORMANCE SPECIFICATIONS


Keystone Catalog Number	Base Type	Rated Lamp Wattage	Legacy Equivalent Wattage	Color Temp	Lumens	Efficacy	Input Voltage	CRI	Beam Angle	Dimmable
KT-LED9.5A19-O-827	E26	9.5W	60W halogen	2700K	800	84 lm/W	120V	>80	230°	Yes
KT-LED9.5A19-O-830	E26	9.5W	60W halogen	3000K	800	84 lm/W	120V	>80	230°	Yes
KT-LED9.5A19-O-835	E26	9.5W	60W halogen	3500K	800	84 lm/W	120V	>80	230°	Yes
KT-LED9.5A19-O-840	E26	9.5W	60W halogen	4000K	800	84 lm/W	120V	>80	230°	Yes
KT-LED9.5A19-O-850	E26	9.5W	60W halogen	5000K	800	84 lm/W	120V	>80	230°	Yes

KEYSTONE SINCE 1945 LIGHT MADE EASY

ESSENTIAL SERIES
GENERAL PURPOSE LED BULBS

KT-LED9.5A19-O-8XX
REPLACEMENT LAMP

PHYSICAL SPECIFICATIONS



LAMP DIMENSIONS

A (Diameter)	2.36"
B (Length)	4.33"

BASE TYPE: E26 (Medium)

PACKAGING

Carton Quantity	60 pcs
Carton Dimensions	15.55" × 13.07" × 10"
Carton Weight	9.9 lbs

ORDERING INFORMATION

ORDER CODE	EASY CODE	UPC
KT-LED9.5A19-O-827	HMT-55	843654126418
KT-LED9.5A19-O-830	SEG-00	843654126425
KT-LED9.5A19-O-835	ERP-91	843654127552
KT-LED9.5A19-O-840	GWA-29	843654126432
KT-LED9.5A19-O-850	ICQ-61	843654126449

CATALOG NUMBER BREAKDOWN

KT-LED9.5A19-O-8XX

1 2 3 4 5 6 7

1 Keystone Technologies
2 LED Lamp
3 Wattage
4 Lamp Shape
5 Omni-Directional
6 80 CRI
7 CCT