Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

LED9A19DIM0830UR 9W Led A19 30K Dim 800LM

Sylvania-Ledvance

Catalog Number	LED9A19DIM0830UR
Manufacturer	Sylvania-Ledvance
Description	Led A19, 9W, Dimmable, 80CRI, 800 Lumen, 3000K, 15000 Life, E26 Medium Base, Frosted Finish
Weight per unit	0.3100 (lbs/each)
Product Category	Led A-Line A Shape Lamps

Features

average life	15000
Base	E26 Medium
dimmable	Yes
Lamp Type	LED A19
lumens	800
Shape	A19
Voltage	120.00 V
Voltage Rating	120.00
Wattage	9.00

Material, Color, and Finish

color rendering index (cri)	80
color temperature	3000
Style	A-shape

Dimensions and Weight

Size	2.36

Descriptions

Description	9W LED A19 30K DIM 800LM
extra long description	SYL LED9A19DIMO830URP/40043 LED9A19
Long Description	LED A19, 9W, Dimmable, 80CRI, 800 Lumen, 3000K, 15000 Life, E26 Medium Base, FROSTED Finish
Product Type	LED9A19DIMO830URP 6/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135400438
Manufacturers Part Number	LED9A19DIMO830URP/40043
sub brand	Ultra
UPC	046135400438

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	LED A-LINE SHAPE LAMPS

Packaging

Carton	6
Package	1
Weight Per each	0.31

Uses, Certifications, and Standards

standard	CSA