

Cooper Lighting by FateN



Emergency Lighting



LEMROLED Emergency Light with Rotatable Optics


Features

- Aesthetic, compact, thin profile design blends into commercial spaces
- AccuLED adjustable optics optimize coverage up to 25'
- EZ Hang simplifies installation and reduces labor
- EZ Key battery disconnect simplifies installation and protects the battery
- Five-year product warranty
- Fifteen-year prorated battery warranty
- Maintenance-free NiCad battery and LED
- UL 924 damp location listed; 0°C to 40°C rated; 120V/277V

ORDERING INFORMATION

SAMPLE NUMBER: LEMRO

Emergency Light	Color	
LEMRO=Two head unit; No remote capability	[Blank]=White	



Emergency Lighting



LEMLED Emergency Light

Features

- AccuLED adjustable optics optimize spacing up to 29' less fixtures required
- EZ Hang simplifies installation and reduces labor
- EZ Key battery disconnect simplifies installation and protects the battery
- Drives up to four remote heads
- Eagle Eye[™] self-diagnostics option available
- Five-year product warranty
- Fifteen-year prorated battery warranty
- Maintenance-free NiCad battery and LED
- UL 924 damp location listed; 0°C to 40°C rated; 120V/277V

ORDERING INFORMATION

SAMPLE NUMBER: LEM4SD

Emergency Light	Color	Option
LEM=Two head unit; No remote capability LEM2=Two head unit; Two head remote capability LEM4=Two head unit; Four head remote capability	[Blank]=White BK=Black	SD=Eagle Eye Self Diagnostic*


^{*} Self Diagnostic option unit comes with Time Delay capability by following installation instructions.




LEM2 / LEM4

LED Emergency Light with Remote Capability

LEM



LEM2 / LEM4



Remotes



LEMR1Single Head LED Remote

Features

- · AccuLED adjustable optics optimize spacing up to 29'
- EZ Click RJ45 connection option reduces installation time
- Class 2 UL rating enables elimination of conduit and J-box in most applications
- 6V option available for non PathLinx fixtures
- Five-year product warranty
- UL 924 damp location listed

ORDERING INFORMATION


SAMPLE NUMBER: LEMR2


Emergency Light	Color
LEMR1=Single Head; Damp Location LEMR2=Double Head; Damp Location 6LEM85=6V; Single Head; Damp Location; No Ethernet 6LEM85D=6V; Double Head; Damp Location; No Ethernet	[Blank]=White BK=Black




LEMR2Double Head LED Remote


Single Head Remote





Double Head Remote







Weatherproof Remotes



LEMWR1

Single Head Weatherproof LED Remote

Features

- · AccuLED adjustable optics optimize spacing up to 29'
- EZ Click RJ45 connection option reduces installation time
- Class 2 UL rating enables elimination of conduit and J-box in most applications
- 6V option available for non-PathLinx fixtures
- Five-year product warranty
- UL 924 wet location listed

ORDERING INFORMATION

SAMPLE NUMBER: LEMR2


Emergency Light	Color
LEMWR1=Single Head; Wet Location LEMWR2=Double Head; Wet Location 6LEM85W=6V; Single Head; Wet Location; No Ethernet 6LEM85DW=6V; Double Head; Wet Location; No Ethernet	[Blank]=White BK=Black




LEMWR2

Double Head Weatherproof LED Remote

Wet Location Remote





Product Features



EZ Click RJ 45 Connection

The EZ Click RJ 45 / Ethernet connection option reduces the cost of labor and materials through an internal power connection. The Class 2 connection avoids the labor and expense associated with conduit and junction box infrastructure (code dependent). PathLinx remotes can also be connected in series via low voltage DC.



EZ Key Power Disconnect

The patented EZ Key is an external battery disconnect that allows the product to be shipped with the battery connected internally. This prevents battery drain during the construction cycle to ensure that the battery isn't damaged and is fully charged for inspection. EZ Key also saves the labor of internally connecting the battery after construction is complete.



EZ Hang Installation Feature

The EZ Hang feature allows the installer to mount the back plate first so that both hands are available for wiring. The fixture hangs from the back plate during the wiring process and then snaps into place.



AccuLED Optics

Patented AccuLED precision engineered optics display sharp cutoffs and an oval light pattern. This optimizes the path of egress per UL924 standards, resulting in fewer fixtures required as compared to similarly priced competitive products. The lens swivel feature within the AccuLED optics provide the opportunity of forward-throw of egress lighting and has a full 360° of rotation.



Technical Information


Fixture	Accu LED Optic Coverage	EZ Hang Installaiton		
LEMR0	25'	Yes	Yes	No
LEM	29'	Yes	Yes	No
LEM 2	29'	Yes	Yes	2
LEM 4	29'	Yes	Yes	4

Fixture	Eagle Eye SD Option	Dimensions 3D	Warranty Fixture	Battery
LEMR0	No	6.5" x 6.18"x1.8"	5 year	15 pro rated
LEM	Yes	6.5"x5.87 " x2.0"	5 year	15 pro rated
LEM 2	Yes	7.5"x7.5"x2.0"	5 year	15 pro rated
LEM 4	Yes	7.5"x7.5"x2.0"	5 year	15 pro rated

Remotes	Accu LED Optic Coverage	UL 924 Rating	EZ Click Option	Compatible with	Warranty Fixture
LEMR1	14.5'	Damp location	Yes	LEM 2/4	5 year
LEMR2	29'	Damp location	Yes	LEM 2/4	5 year
6LEM85	14.5'	Damp location	No	Any 6V	5 year
6LEM85D	29'	Damp location	No	Any 6V	5 year
LEMWR1	14.5'	Wet location	Yes	LEM 2/4	5 year
LEMWR2	29'	Wet location	Yes	LEM 2/4	5 year
6LEM85W	14.5'	Wet location	No	Any 6V	5 year
6LEM85DW	29'	Wet location	No	Any 6V	5 year

Expanded Fixture Spacing

The utilization of LED technology has allowed Sure-Lites to increase the distance between PathLinx fixtures, while meeting UL924 standards for egress lighting. PathLinx products have spacing capabilities that are up to 50% greater than traditional incandescent emergency lighting, reducing the overall cost of egress lighting.



Eaton's Cooper Lighting Business

Headquarters

1121 Highway 74 South Peachtree City, GA 30269

P: 770-486-4800

www.cooperlighting.com

Canada Sales

5925 McLaughlin Road

Mississauga, Ontario L5R 1B8

P: 905-501-3000

F: 905-501-3172

Our Lighting Product Brands

Halo

Halo Commercial

Portfolio

IRiS

RSA

Metalux

Corelite

Neo-Ray

Fail-Safe MWS

Ametrix

Shaper

io

Lumark

McGraw-Edison

Invue

Lumière

Streetworks

AtLite

Sure-Lites

Our Controls Product Brands

Greengate iLumin

Zero 88

Fifth Light Technology iLight (International Only)

Eaton

1000 Eaton Boulevard Cleveland, OH 44122 United States Eaton.com

Eaton's Cooper Lighting Business

1121 Highway 74 South Peachtree City, GA 30269 P: 770-486-4800 www.cooperlighting.com

© 2014 Eaton All Rights Reserved Printed in USA Publication No. ADX140001 January 2014

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

