

PROJECT NAME:_	_CATALOG NUMBER:_	

NOTES: FIXTURE SCHEDULE:_

Page: 1 of 2

LED FAUX CAN

LFC Series













PRODUCT DESCRIPTION:

LED Faux Cans accomplish the task of recessed downlighting without requiring installers to use a recessed can. Faux Cans are mountable to a 4-inch junction box. An optional mounting bracket allows existing recessed cans to be retrofitted with the faux can, for an easy upgrade to LED lighting.

Featuring driverless technology that increases performance and reliability, LED Faux Cans are equivalent up to 75W PAR 30 halogen lamp and offer vivid color rendering. They are wetlisted, making them suitable for virtually any application that requires downlighting.

FEATURES:

- Mounts to a 4" junction boxes Achieve Recessed Down lighting without using a bulky can
- Vivid Color Rendering 90+ CRI standard
- Optional Mounting Bracket allows Recessed Cans to be retrofitted with the LED Faux Can
- No Driver Key point of failure in LED systems is completely eliminated
- CSA Wet Listed Install it virtually anywhere
- Dimmable with many Triac controls (visit website for complete

MODEL SELECTION (Fu	Il list of order codes on pg. 2) Typical order examp	le: LFC61527W/V2		
LFC			w	/V2
FAMILY	SIZE & WATTAGE (NOMINAL)	сст	COLOR	VERSION
LFC= LED Faux Can	413= 4 inches and 13W, replaces 50W Halogen 615= 6 inches and 15W, replaces 75W Halogen	27= 2700K 30= 3000K 41= 4100K	W= White	N2= Version 2

ACCESSORIES						
ORDER CODE	MODEL NUMBER DESCRIPTION		MODEL NUMBER DESCRIPTION IN		IMAGE	
74006	LFC4-BRACKET	LED Faux Can Bracket for 4" Recessed Fixtures				
74005	LFC6-BRACKET	LED Faux Can Bracket for 6" Recessed Fixtures				

6"

COMPATIBLE DIMMERS:

MAKE	DIMMER MODEL		
Lutron	CTCL-153PD		
Lutron	LGCL-153PL		
Lutron	DVELV-300P		
Smart Home	2876D		

MAKE	DIMMER MODEL		
Leviton	IPL06		
Leviton	SureSlide		
Leviton	IPL10		

NOTES:

1. Edison base adapter is not included





LED FAUX CAN LFC Series

Page: 2 of 2

SPECIFICATIONS:		LFC41327 W/V2	LFC41330 W/V2	LFC41341 W/V2	LFC61527 W/V2	LFC61530 W/V2	LFC61541 W/V2	
ITEM	SPECIFICATION	DETAILS						
	Power Consumption (W)	12.0	12.0	12.0	14.7	15.0	15.6	
	Lumens Delivered (lm)	860	860	860	1,000	1,000	1,000	
GENERAL	Efficacy (Im/W)*	75	75	75	67	67	67	
PERFORMANCE	CRI	≥90						
	Color Temperature (K)	2700K	3000K	4100K	2700K	3000K	4100K	
	L70 Lifetime (hours)	30,000						
EL ESTRICAL	Power Factor	>0.99 @ 120V						
ELECTRICAL	Input Voltage	120V						
DI IVOIO AI	Weight	2 lbs						
PHYSICAL	Operating Temperature	0°F to 104°F						
	Certification	Energy Star, CSA, FCC, LM-79, LM-80						
OFFICION	Material Usage	RoHS compliant; no mercury						
CERTIFICATION	Environment	Indoor & Outdoor						
	Warranty	5 years						

^{*} Measured at the light source as per Energy Star testing requirements

ORDERING*:

31D21(III) 1						
ORDER CODE	MODEL	WATTAGE	FINISH	VOLTAGE	ССТ	
95548	LFC41327W/V2	13				2700K
95549	LFC41330W/V2				3000K	
95550	LFC41341W/V2			\M/laita	120	4100K
76476	LFC61527W/V2	15	White	120	2700K	
95459	LFC61530W/V2				3000K	
95460	LFC61541W/V2				4100K	

^{*}Please contact your MaxLite representative to order products that don't have order codes listed here.

Phone: 1-800-555-5629 | Fax: 973-244-7333 | Web: www.maxlite.com | E-mail: info@maxlite.com | Revised: 09-19-17