



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LFV1010Q Highland Locking Fork Terminal, -40 - 221 Degrees *Minnesota Mining (3M)*

Catalog Number	LFV1010Q
Manufacturer	Minnesota Mining (3M)
Description	Locking Fork, #12 Awg Conductor Size, #10 Awg Conductor Size, Insulated, Vinyl Insulation Material, Yellow Insulation Color, 0.11 LB
Weight per unit	0.1100 (lbs/each)
Product Category	Small Terminals & Connectors

Descriptions

Description	HIGHLAND LOCKING FORK TERMINAL, -40 - 221 DEGREES
extra long description	3M 7010350240 3M™ Highland™ Vinyl I
Features	3M™ Highland™ Locking Fork Terminal is color-coded for quick and easy identification of the wire size required. It has a butted-seam barrel that is covered by a funnel-designed, rigid-molded, polyvinyl chloride sleeve to guide the wire into position while providing electrical contacts and mechanical stress relief at the point of insulation. The abrasion-resistant, flared, vinyl-sleeve insulation ensures easy crimping. UL Listed, CSA Certified and RoHS 2011/65/EU Compliant.

Manufacturer Information

Brand	Highland
GTIN	00051128600146
Manufacturers Part Number	LFV1010Q
UPC	051128600146

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	LOCKING

Packaging

Carton	1
Package	10
Weight Per each	0.11

Uses, Certifications, and Standards

standard	UL and CSA
----------	------------