

Eaton LGH3600FAG

Catalog Number: LGH3600FAG

Eaton Series G molded case circuit breaker, LG-frame, LG, Fixed thermal, adjustable magnetic trip, Three-pole, 600 A, 600 Vac, 100 kAIC at 240 Vac, 70 kAIC at 415 Vac, 65 kAIC at 480 Vac, 35 kAIC at 600 Vac, Line and load, Metric



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Series G complete molded case circuit breaker	LGH3600FAG
	UPC
	782116142781

Product Length/Depth	Product Height
4.09 in	10.13 in

Product Width	Product Weight
5.48 in	16 lb

Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year CE Marked from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications
	UL Listed
	IEC Rated
	CSA Certified

Catalog Notes
LG breaker is HACR rated

defaultTaxonomyAttributeLabel

Type

Complete breaker

Amperage Rating

600 A

Voltage rating

600 Vac

Trip Type

Fixed thermal, adjustable magnetic

Circuit breaker type

LG

Circuit breaker frame type

Complete breaker

Terminals

Line and load

Frame

LG

Mounting hardware

Metric

Interrupt rating

70 kAIC at 415 Vac

100 kAIC at 240 Vac

65 kAIC at 480 Vac

35 kAIC at 600 Vac

Number of poles

Three-pole

Resources

Application notes

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

[Application of Tap Rules to Molded Case Breaker Terminals](#)

Brochures

[Motor protection circuit breakers product aid](#)

[High performance operating handles for Series G circuit breakers product aid](#)

[Multi-wire lugs product aid](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

[StrandAble terminals product aid](#)

[Series G MCCB quick selector](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[Current limiting molded case circuit breaker module product aid](#)

[Molded case circuit breakers providing higher levels of selective coordination product aid](#)

[Comprehensive circuit protection for control panel applications](#)

[Current limiting molded case circuit breaker module for series G, JG and CL](#)

[Circuit breaker motor operators product aid](#)

[J-Frame 310+ and L-Frame 310+ Molded-case circuit breakers](#)

[Breaker service centers](#)

Catalogs

[Molded case circuit breakers catalog](#)

[Eaton's Volume 4—Circuit Protection](#)

Drawings

[LG-frame Molded Case Circuit Breaker Drawing](#)

Installation instructions

[Installation Instructions for Series G L-Frame Circuit Breakers](#)

Specifications and datasheets

[L-Frame 310+ Molded-case circuit breakers 100A-600A](#)

[Eaton Specification Sheet - LGH3600FAG](#)

[NG and ND-Frame molded case circuit breakers](#)

[MOEM MCCB product selection guide](#)

Time/current curves

[Series G, L-frame Time Current Curves](#)

Warranty guides



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)