



Commercial, Industrial and Residential Electrical Products

LED Swivel Floodlight, 1200 Lumens, Bronze

Catalog #: LL1200Z



FEATURE BENEFIT

Commerical-grade LED swivel flood light perfect for residential or commercial applications

PRODUCT FEATURES

- 85% less energy consumption compared to incandescent bulb with simliar light
- Uses only 13W
- 1200 Lumens (equivalent to 75W incandescent) of 3000k warm white light
- Rugged die-cast aluminum heads
- 120/277 VAC 50/60 Hz
- Unique locking swivel joint for easy light adjustment
- Long life up to 50,000 hours
- 6 In. lead wires
- Tempered glass lens
- Tool-free mounting to Bell boxes, covers and cluster covers
- DLC Listed

APPLICATIONS

Attractive and durable floodlight will bring years of enjoyment, safety and convenience for various architectural or landscape lighting needs

CERTIFICATIONS



PRODUCT SPECIFICATIONS

UPC Number: 050169994795

 Ea Length/Depth (in.):
 2.25

 Ea Width (in.):
 2.25

 Ea Height (in.):
 5.625

 Wt. Ea. (Lbs.):
 1.013

 Package Type:
 Box

 Package Contents:
 1

 Product UPC-A Labeled:
 Yes

SHIPPING

I2of5: 50050169994790

Standard Carton Qty:
Min Order Qty:

▲ WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov.

Revision 2, March 2020



BELL Tempe, AZ 85281 480-921-7552 www.hubbell.com/bell/en

