



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1001 South Goode  
79701-0000, TX Midland  
Phone: 432-685-3108  
Fax: 432-685-3706



## LML01 3/8" Sealtight 90DEG Conn

*Appleton/Oz Gedney*

Catalog Number	LML01
Manufacturer	Appleton/Oz Gedney
Description	Conduit Fittings, LML 90 Liquidtight Connectors, Material: Zinc Diecast, UI Standard: 514B, Trade Size: 3/8-1/2, Dimension: Height 2.40 Inches, Width 2.15 Inches, Thread Length .53
Weight per unit	0.2000 (lbs/each)
Product Category	Liquid Tight Fittings

### Features

angle	90
connection	Male NPS Thread
Connector Type	Compression
insulation	False
Material	Zinc Die Cast

### Material, Color, and Finish

Color	Metallic
Finish	Natural

### Dimensions and Weight

Size	0.375
------	-------

### Descriptions

Description	3/8" SEALTIGHT 90DEG CONN
extra long description	EGS LML-01 3/8 IN 90D CONN LFMC/LFN
Long Description	Conduit Fittings, LML 90 Liquidtight Connectors, Material: Zinc Diecast, UL Standard: 514B, Trade Size: 3/8-1/2, Dimension: Height 2.40 Inches, Width 2.15 Inches, Thread Length .53
Product Type	3/8 In 90D Conn LFMC/LFNC
Special Features	2.15 IN Length X 2.4 IN Height, 0.53 IN Thread Length, For Liquidtight Flexible Metal Conduit and Type B Non-Metallic Conduit, Liquidtight/Raintight/Oiltight

### Manufacturer Information

Brand	Appleton
GTIN	00687855383016
Manufacturers Part Number	LML01
UPC	687855383016

### Taxonomies, Classifications, and Categories

Category Description	METALLIC FITTINGS
Type	90 Deg Liquid Tight Conduit Connector



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1001 South Goode  
79701-0000, TX Midland  
Phone: 432-685-3108  
Fax: 432-685-3706

## Trade Size

Trade Size ..... 0.5

## Packaging

Carton ..... 10

Package ..... 50

Weight Per each ..... 0.2

## Uses, Certifications, and Standards

Application ..... For Terminating Liquidtight Flexible Metal Conduit to a Enclosure  
at a 90 Degree Angle

environmental conditions ..... Rain Tight, Oil Tight, Liquid Tight

nema rating ..... FB-1

standard ..... CSA Certified: 208044;CSA Standard: C22.2 No. 18.3;NEMA:

FB-1;UL Listed: E32539;UL Standard: 514B