

Eaton Bussmann series LP-CC fuse

LP-CC-20

UPC:051712180276

Dimensions:

- **Height:** .41 IN
- **Length:** 1.5 IN
- **Width:** .41 IN

Weight:.15 LB

Warranties:

- Not Applicable

Specifications:

- **Type:** Current-limiting, Time-delay
- **Special Features:** Rejection Style
- **Application:** Specialized circuits and industrial control
- **Voltage Rating:** 600 Vac, 300 Vdc
- **Amperage Rating:** 20A
- **Interrupt Rating:** 200 kAIC at 600 Vac, 20 kAIC at 300 Vdc
- **Class:** Class CC
- **Connection:** Ferrule end X ferrule end
- **Material Type:** Melamine tube
- **Packaging Type:** Standard
- **Diameter:** .40625 IN
- **Quantity:** Carton: 10
- **Fuse Indicator:** Non Indicating
- **Response Time:** 12s at 200%
- **Number Of Elements:** Dual

Supporting documents:

- [Product Catalog](#)
- [LOW PEAK CC TIME DELAY](#)
- [Product Datasheet](#)

Certifications: No Data

Product compliance:

- CE Marked
- RoHS Compliant

© 2016 Eaton. All rights reserved.