

# LQ75-GY8

Incandescent and Halogen quartz replacement lamps.

Color: N/A

Weight: 0.2 lbs

## Lamp Info

Type: T4  
Watts: 75W  
Shape/Size: N/A  
Base: Bi-Pin GY8.0  
ANSI: N/A  
Hours: 1,500  
Lamp Lumens: 1,500  
Efficacy: N/A

## Ballast Info

Type: N/A  
120V: N/A  
208V: N/A  
240V: N/A  
277V: N/A  
Input Watts: 0W  
Efficiency: N/A



## Technical Specifications

### Patents:

RAB sensor and fixture designs are protected under U.S. and International Intellectual Property laws.