

Non-metallic Type B liquid tight fittings

For use with Carflex™ conduit

Carflex[®]





01 LT fitting - straight 02 LT fitting - 90 degrees

Features & Benefits:

• Meets UL 514B for liquid-tight fittings

02

- Straight and 90° liquid-tight fittings
- Trade sizes from 3/8" to 2" (12mm to 53mm)
- NPT Threads
- UL Listed for wet locations
- Nitrile o-ring helps provide liquid-tight connection
- Non-conductive and non-corrosive
- Easy to install

Applications:

- For use with liquid-tight flexible non-metallic type-B conduit only
- Suitable for use with Carflex[®] conduit, providing a full non-metallic system solution
- Industrial applications

Construction / Material / Finish:

- Gland Nut: Thermoplastic Polymer
- Sealing Ring: Flexible PVC
- Bushing: Thermoplastic Polymer
- Gasket: Neoprene
- Body: Thermoplastic Polymer
- O-Ring: Nitrile rubber
- Locknut:
 - 3/8" to 1" Zinc-plated steel
 - 1 ¼" to 2" PVC

Liquid-tight fittings that meet the demands for wet locations

Certifications / Standards:



3-Part Specification: 26 05 33.27 End User Tools



 UL 514B, Fittings for Cable and Conduit – File: E23018

Environment ratings:

Working Temperature:

• Gen: Up to 225° F (107° C)

Chemical Resistance Guide:

- See Publication TDS000081 (Fittings: Steel, Iron & PA66 Polyamide)
- See Publication TDS000117 (Liquid-tight Flexible Metal Conduits)

Product selection

Carflex™ Type B Liquidtight Fittings

Trade size				Thread Type	Straight	90°	
Inches	Metric	ISO BS EN	Standard	Size	Part no.	Part no.	
3/8"	12mm	16mm	NPT	3/8"	LT43C	LT20C	
1/2"	16mm	20mm	NPT	1/2"	LT43D-NEW	LT20D-NEW	
3/4"	21mm	25mm	NPT	3/4"	LT43E-NEW	LT20E-NEW	
1"	27mm	32mm	NPT	1"	LT43F-NEW	LT20F-NEW	
11/4"	35mm	40mm	NPT	11/4"	LT43G	LT20G	
11/2"	41mm	50mm	NPT	11/2"	LT43H	LT20H	
2"	53mm	63mm	NPT	2"	LT43J	LT20J	

Drawing			Trade size			Inches		Millimeters			Weight
	Inches	Metric	ISO BS EN	Α	В	с	А	В	с	lbs.	kg
Carflex™ Type B LT Straight Fit	tings - NPT Th	eads									
	3/8"	12mm	16mm	13/8"	1"	1/2"	35.6	26.7	13.9	0.09	0.04
	1/2"	16mm	20mm	13/8"	1"	1/2"	35.6	26.9	14.2	0.08	0.04
	3/4"	21mm	25mm	111/16"	13/8"	1/2"	43.4	33.5	14.2	0.13	0.06
A C H	1"	27mm	32mm	2"	11/2"	3/4"	51.8	38.1	17.8	0.16	0.07
	11⁄4"	35mm	40mm	21/2"	11/8"	11/16"	63.5	29.5	18.0	0.27	0.12
	11/2"	41mm	50mm	23⁄4"	13/8"	3/4"	70.6	34.5	19.1	0.33	0.15
BC	2"	53mm	63mm	33⁄8"	11/2"	7⁄8"	84.6	36.8	23.1	0.41	0.19
Carflex™ One-piece LT 90° Fitt	ings - NPT Thre	ads									
← A→	3/8"	12mm	16mm	11/2"	17/16"	17/16"	39.6	36.6	36.6	0.11	0.05
	1/2"	16mm	20mm	15/8"	13/4"	2"	41.1	44.7	52.1	0.09	0.04
$h \rightarrow d$	3/4"	21mm	25mm	11/8"	2"	23/8"	47.8	51.8	59.7	0.14	0.06
	1"	27mm	32mm	21⁄4"	2"	2"	57.4	51.1	51.1	0.24	0.11
	11⁄4"	35mm	40mm	21⁄2"	21/2"	31⁄2"	63.0	63.5	90.2	0.30	0.14
	11/2"	41mm	50mm	23⁄4"	213/16"	4"	70.4	71.1	101.1	0.41	0.19
 − B → C 	2"	53mm	63mm	35/16"	31⁄2"	4%/16"	84.6	88.4	115.8	0.59	0.27

Note: • Dimensions for reference only. • Product must be installed in accordance with applicable national and local electrical codes.

tnb.abb.com (US/Latin America) tnb.ca.abb.com (Canada) abb.com

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction - in whole or in part - is forbidden without prior written consent of ABB. © 2022 ABB Installation Products Inc. and/or its related companies. All Rights Reserved.