



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LT34 3/4" Met L/T, Non UL 100'

Southwire Company

Catalog Number	LT34
Manufacturer	Southwire Company
Description	Liquidtight Flexible Conduit, 3/4 In Trade Size, 1.03 to 1.05 In Conduit Outer Diameter, 0.82 to 0.84 In Conduit Inner Diameter, Titan(R) Ef Style, 100 FT Length, Galvanized, Gray, 5 In Bend Radius, +14 °F Operating Temperature, +140 °F Operating Temperature, 29 LB/100 FT
Weight per unit	0.2700 (lbs/each)
Product Category	Liquid Tight Conduit

Features

outside diameter	1035
------------------	------

Dimensions and Weight

Diameter	3/4"
----------	------

Descriptions

Description	3/4" MET L/T, NON UL 100'
extra long description	SWC 55094003 Titan2 Type EF Extra-F

Manufacturer Information

GTIN	00032886042478
UPC	032886042478

Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
----------------------	--------------

Availability

minimum qty	100
-------------	-----

Packaging

Carton	100
Weight Per each	0.27