



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3520 S Sam Houston Pkwy East Suite 900
77047-0000, TX Houston
Phone: 281-412-7049
Fax: 281-412-7314



LT4 4" Met L/T, Non UL 25' *Southwire Company*

Catalog Number	LT4
Manufacturer	Southwire Company
Description	Liquidtight Flexible Conduit, 4 In Trade Size, 4.46 to 4.5 In Conduit Outer Diameter, 4 to 4.04 In Conduit Inner Diameter, Titan(R) Ef Style, 25 FT Length, Galvanized, Gray, 24 In Bend Radius, +14 °F Operating Temperature, +140 °F Operating Temperature, 306 LB/100 FT
Weight per unit	2.5 (lbs/each)
Product Category	Liquid Tight Conduit

Features

outside diameter	4370
------------------	------

Dimensions and Weight

Diameter	4"
----------	----

Descriptions

Description	4" MET L/T, NON UL 25'
extra long description	SWC 55107601 Titan2 Type EF Extra-F

Manufacturer Information

GTIN	00032886043154
UPC	032886043154

Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
----------------------	--------------

Packaging

Carton	25
Weight Per each	2.5