



LTC050 1/2" PVC Smooth NM LT Conduit

Abb Installation Products, Inc

Catalog Number	LTC050
Manufacturer	Abb Installation Products, Inc
Description	Industrial Grade, Type B Liquidtight Flexible PVC Conduit, 1/2 Inch Conduit Size, Approved For Outdoor and Direct Burial In The Us, UL Temperature Ratings - 105 Degrees C Dry, 60 Degree C Wet, 70 Degree C Oil, CSA Temperature Rating 18 to 75 Degrees C, Oil Resistant, Voltage Rating 600V, Black With Orange Markings
Weight per unit	0.1310 (lbs/each)
Product Category	Liquid Tight Fittings

Features

Inside Diameter	0.622
outside diameter	0.8386
Voltage Rating	600 V

Material, Color, and Finish

Color	Black
-------	-------

Dimensions and Weight

Length	1200.7874
--------	-----------

Descriptions

Also Known As...	Carflex®
Description	Liquid Tight Conduit
extra long description	1/2" PVC SMOOTH NM LT CONDUIT
Long Description	ABB LTC050 1/2IN LT TYPE B COND PVC
Product Type	Industrial Grade, Type B Liquidtight Flexible PVC Conduit, 1/2 Inch Conduit Size, Approved for Outdoor and Direct Burial in the US, UL Temperature Ratings - 105 Degrees C Dry, 60 Degree C Wet, 70 Degree C Oil, CSA Temperature Rating 18 to 75 Degrees C, Oil Resistant, Voltage Rating 600V, Black with Orange Markings
similar brands	1/2IN LT Type B Cond PVC BLK
Special Features	Sealtite® The Smooth Inner Surface Ensures that Cables and Conductors Can Be Fed Through Very Easily



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	T&B Ind Fitting
GTIN	00786210789545
Manufacturers Part Number	LTC050
UPC	786210789545

Taxonomies, Classifications, and Categories

Category Description	NON-METALLIC SEALITE AND FITTINGS
Type	Liquidtight Flexible Non-Metallic Conduit

Trade Size

Trade Size	1/2 in
------------	--------

Availability

minimum qty	100
-------------	-----

Packaging

Carton	100
Weight Per foot	0.131

Uses, Certifications, and Standards

Application	Machine Tools, Motor Hookups, Food Processing Equipment, Extensions from Wire Ways, and Sensor and Micro Switch Wiring Found In Control Consoles
standard	UL E95745, CSA