


## for PVC Jacketed MC Cable • One Fitting Fits Multiple Cable Sizes



- 1 Remove sharp edges from end of MC cable. Cut 1-1/4" off the PVC jacket to prepare cable for installation of fitting.
- 2 Determine which grommet to use. When assembled, push cable into fitting.



3 Cable installed in fitting. Tighten nut.



4 Install assembly in box



I TMC50 0715/15M

Exploded View on cable

Save time and money with Arlington's liquid-tight, concrete-tight zinc fittings for PVC jacketed MC cable. They come with grommets and washers that allow this SINGLE fitting to fit three cable sizes!

The 1/2" LTMC50 ships ready to install on #12 or #14 PVC jacketed MC cable. For installations on #10 cable, substitute the WHITE grommet and washer. It's FAST and EASY!

Because they fit more than one cable size, these cable fittings reduce inventory, saving you the cost of stocking several different fittings.

- Heavy-duty zinc diecast construction
- 1/2" trade size
- UL Listed

LTMC50

		DESCRIPTION 1/2" Trade Size	UNIT PKG	STD PKG
LTMC50	04279 F	Zinc Fitting for 1/2" VC Jackected MC Cab		100
MC Cable Range:		.415" to .565"		
Overall jacket OD Range:		.540" to .665"		

Includes zinc fitting, black grommet and washer (installed) and white grommet and washer

