



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LU1000ECO 1000W E25 High Pressure Sodium Clear Mogul Base

Ge By Current Lamps

Catalog Number	LU1000ECO
Manufacturer	Ge By Current Lamps
Description	High Pressure Sodium Lamp, 22, 2100 K, 140000 LM Brightness (Lumens), 1000 W, 456 V, Clear, Glass Material, 24000+ H Average Life, Mogul Base, S52 Ansi Ballast Code, Non Dimmable, 3.125 In Diameter, 15.06 In Length, 24.75 % Mercury Content, 0.96 LB
Weight per unit	0.9600 (lbs/each)
Product Category	Hid High Pressure Sodium Lamps

Features

Base	E39
lumens	130000

Material, Color, and Finish

Color	Clear
color rendering index (cri)	20-39
Style	Open or enclosed fixtures

Descriptions

Description	1000W E25 HIGH PRESSURE SODIUM CLEAR MOGUL BASE
extra long description	GEL LU1000/ECO 44058 LUCALOX
Special Features	15.06IN Length

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168440585
UPC	043168440585

Taxonomies, Classifications, and Categories

Category Description	SODIUM
----------------------	--------

Packaging

Carton	1
Package	6
Weight Per each	0.96

Uses, Certifications, and Standards

Application	Universal burning position
-------------	----------------------------