



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LU15055HECO 150W ED23.5 High Pressure Sodium Clear Mogul Base

*Ge By Current Lamps*

Catalog Number	LU15055HECO
Manufacturer	Ge By Current Lamps
Description	High Pressure Sodium Lamp, 22, 2000 K, 16000 LM Brightness (Lumens), 150 W, 110 V, Clear, Glass Material, 24000 H Average Life, E39 Mogul Screw Base, S55 Ansi Ballast Code, Non Dimmable, 2.95 In Diameter, 7.75 In Length, 14.85 % Mercury Content, 0.36 LB
Weight per unit	0.3600 (lbs/each)
Product Category	Hid High Pressure Sodium Lamps

### Features

Base	E39
lumens	16000
Wattage	150

### Material, Color, and Finish

Color	Clear
color rendering index (cri)	20-39
Style	Open or enclosed fixtures

### Descriptions

Description	150W ED23.5 HIGH PRESSURE SODIUM CLEAR MOGUL BASE
extra long description	GEL LU150/55/H/ECO 85371 LUCALOX
Special Features	7.75IN Length

### Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168853712
Manufacturers Part Number	LU150/55/H/ECO
UPC	043168853712

### Taxonomies, Classifications, and Categories

Category Description	SODIUM
----------------------	--------

### Packaging

Carton	1
Package	12
Weight Per each	0.36

### Uses, Certifications, and Standards

Application	Universal burning position
-------------	----------------------------