ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

LU15055HEC0 150W ED23.5 High Pressure Sodium Clear Mogul Base

Ge By Current Lamps

Catalog Number	LU15055HEC0
Manufacturer	Ge By Current Lamps
Description	High Pressure Sodium Lamp, 22, 2000 K, 16000 LM Brightness (Lumens), 150 W, 110 V, Clear, Glass Material, 24000 H Average Life, E39 Mogul Screw Base, S55 Ansi Ballast Code, Non Dimmable, 2.95 In Diameter, 7.75 In Length, 14.85 % Mercury Content, 0.36 LB
Weight per unit	0.3600 (lbs/each)
Product Category	Hid High Pressure Sodium Lamps

Features

Base	E39
lumens	16000
Wattage	150

Material, Color, and Finish

Color	Clear
color rendering index (cri)	20-39
Style	Open or enclosed fixtures

Descriptions

Description	150W ED23.5 HIGH PRESSURE SODIUM CLEAR MOGUL BASE
extra long description	GEL LU150/55/H/ECO 85371 LUCALOX
Special Features	7.75IN Length

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168853712
Manufacturers Part Number	LU150/55/H/ECO
UPC	043168853712

Taxonomies, Classifications, and Categories

Category Description	SODIUM

Packaging

Carton	1
Package	12
Weight Per each	0.36

Uses, Certifications, and Standards

Application	Universal burning position