ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

IMAGE COMING SOON

# LU400SUPER5KIT Ballast Lamp

*Sylvania-Ledvance*

| | |
|---|---|
| Catalog Number | LU400SUPER5KIT |
| Manufacturer | Sylvania-Ledvance |
| Description | OBS47647 120/208/240/277/480V 5 Tap Magnetic Core and Coil Ballast For 400W High Pressure Sodium Lamp |
| Weight per unit | 14.5 (lbs/each) |
| Product Category | Lighting |

## Features

| | |
|---|---|
| amperage rating | 3.8/2.2/1.9/1.7/1.0 |
| ANSI Code | S51 |
| Ballast Factor | 1 |
| Lamp Type | HIGH PRESSURE SODIUM |
| Minimum Starting Temperature | -40.000000000000000 |
| Number of Lamps | 1 |
| Power Factor | >0.9 |
| start type | Pulse |
| total harmonic distortion | <20 |
| Voltage Rating | 120, 208, 240, 277, 480 |
| Wattage | 400 |

## Dimensions and Weight

| | |
|---|---|
| Height | 7.108000000000000 |
| Length | 8.700000000000000 |
| Width | 5.900000000000000 |

## Descriptions

| | |
|---|---|
| Description | BALLAST LAMP |
| extra long description | SYL LU400/SUPER5-KIT/47647 LU400SUP |
| Long Description | OBS47647 120/208/240/277/480V 5 tap magnetic core and coil ballast for 400W high pressure sodium lamp |
| Product Type | LU400SUPER5KIT 1/CS 1/Sku |
| Special Features | 5 Tap, Magnetic Core and Coil, Circuit Type Constant Wattage Autotransformer, Input Power 464 WAT |

## Manufacturer Information

| | |
|---|---|
| Brand | OSRAM |
| GTIN | 00046135476471 |
| Manufacturers Part Number | LU400/SUPER5-KIT/47647 |
| UPC | 046135476471 |

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

| | |
|---|---|
| Category Description | HID BALLASTS |
| Type | Magnetic HID Ballast |

## Packaging

| | |
|---|---|
| Carton | 1 |
| Weight Per each | 14.45 |

## Uses, Certifications, and Standards

| | |
|---|---|
| standard | S51 |