ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

LU70EC0MED 70W E17 High Pressure Sodium Clear Med Base Lamp

Ge By Current Lamps

Catalog Number	LU70EC0MED
Manufacturer	Ge By Current Lamps
Description	High Pressure Sodium Lamp, 22, 1900 K, 6400 LM Brightness (Lumens), 70 W, 110 V, Clear, Glass Material, 24000+ H Average Life, Medium Base, S62 Ansi Ballast Code, Non Dimmable, 2.12 In Diameter, 5.43 In Length, 13.7 % Mercury Content, 0.17 LB
Weight per unit	0.1700 (lbs/each)
Product Category	Hid High Pressure Sodium Lamps

Features

Base	E26
lumens	6400
Wattage	70

Material, Color, and Finish

Color	Clear
color rendering index (cri)	20-39
Style	Open or enclosed fixtures

Descriptions

Description	70W E17 HIGH PRESSURE SODIUM CLEAR MED BASE LAMP
extra long description	GEL LU70/MED/ECO 11339 LUCALOX
Special Features	5.43IN Length

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168113397
UPC	043168113397

Taxonomies, Classifications, and Categories

Category Description	SODIUM

Availability

Status	Inactive

Packaging

Carton	1
Package	6
Weight Per each	0.17