



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

15152 E Fremont Dr
80112-0000, CO Centennial
Phone: 720-278-7555
Fax: 720-259-8851



LU70ECOMED 70W E17 High Pressure Sodium Clear Med Base Lamp

Ge By Current Lamps

Catalog Number	LU70ECOMED
Manufacturer	Ge By Current Lamps
Description	High Pressure Sodium Lamp, 22, 1900 K, 6400 LM Brightness (Lumens), 70 W, 110 V, Clear, Glass Material, 24000+ H Average Life, Medium Base, S62 Ansi Ballast Code, Non Dimmable, 2.12 In Diameter, 5.43 In Length, 13.7 % Mercury Content, 0.17 LB
Weight per unit	0.1700 (lbs/each)
Product Category	Hid High Pressure Sodium Lamps

Features

Base	E26
lumens	6400
Wattage	70

Material, Color, and Finish

Color	Clear
color rendering index (cri)	20-39
Style	Open or enclosed fixtures

Descriptions

Description	70W E17 HIGH PRESSURE SODIUM CLEAR MED BASE LAMP
extra long description	GEL LU70/MED/ECO 11339 LUCALOX
Special Features	5.43IN Length

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168113397
UPC	043168113397

Taxonomies, Classifications, and Categories

Category Description	SODIUM
----------------------	--------

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Package	6
Weight Per each	0.17