

# IMAGE COMING SOON

**Product Number:** 47427

**Order Abbreviation:** M1000/SUPER5-KIT

**General Description:** 120/208/240/277/480V 5-tap magnetic core and coil probe start ballast for 1000W probe start metal halide lamp

**\* Full Case Required**

## Product Information

Abbrev. With Packaging Info.	M1000SUPER5KIT 1/CS 1/SKU
ANSI Code	M47
Capacitor Height	5"
Circuit Type	CWA
Nominal Voltage (V)	120/208/240/277/480V
Number of Lamps	1
Open Circuit Voltage (V)	420
Power Factor	>0.9
Primary Lamp Type	M1000
Sound Rating	N
Starting Method	OCV
Starting Temperature - Fahrenheit	-22°F
Starting Temperature - Celsius	-30°C
Total Harmonic Distortion (THD)	<20%
Wiring Method	LEADS



## Footnotes

- Product is a kit containing the core & coil, capacitor, ignitor (where required), brackets and mounting hardware
- Install in accordance with National Electric Codes
- Ground Ballast Core and Metallic Case of Capacitor and Ignitor
- Minimum starting temperature: -20 F / -29 C
- Product contains installation instructions