

Eaton M22-C2-M2V

Catalog Number: M22-C2-M2V

Eaton M22 Assembled two element control station, 22.5 mm, Top: flush, Bottom: extended, Momentary, Non-illuminated, Button: Green, Red, IP66, UL (NEMA) Type 4X, 13



General specifications

Product Name	Catalog Number
Eaton M22 pushbutton control station	M22-C2-M2V
UPC	Product Length/Depth
786685283012	4.72 in
Product Height	Product Width
2.7 in	3.15 in
Product Weight	Warranty
0.468 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Compliances	Certifications
CE Marked	CSA Certified
Bureau Veritas	CCC Marked
GoST-R	Lloyd's Register Certified
Catalog Notes	
25% smaller depth than most competitor enclosures. Imoact resistant polycarbonate enclosure.	

defaultTaxonomyAttributeLabel

Type

Control Station

Actuator function

Momentary

Button color

Green, red

Actuator

Pushbuttons, top: flush, bottom: extended

Environmental rating

IP66, NEMA 4X, NEMA 13

Etching code

GB1, GB0

Orientation

Vertical

Contact configuration

NO, NC

Enclosure color

Gray

Illumination

Non-illuminated

Series

M22

Size

22.5 mm

Base

Black

Inscription

START, STOP

Resources

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - M22-C2-M2V](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)