

Eaton M22-DDLF-GR

Catalog Number: M22-DDLF-GR

Eaton M22 modular pushbutton, 22.5 mm, Flush - dual button actuator, Momentary, Illuminated, Bezel: Silver, Button: Top Green, Bottom Red, IP66, NEMA 4X, 13, Light 100,000 hours, Button 200,000 Operations



Photo is representative

General specifications

Product Name

Eaton M22 modular pushbutton

Catalog Number

M22-DDLF-GR

UPC

786685272191

Product Length/Depth

2.15 in

Product Height

0.52 in

Product Width

1.17 in

Product Weight

0.995 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

CE Marked
GoST-R
Bureau Veritas

Certifications

CSA Certified
CCC Marked
Lloyd's Register Certified

Catalog Notes

Includes contact block mounting adapter.

defaultTaxonomyAttributeLabel

Application

Pushbutton

Special features

M22 series

Type

22.5 mm Modular

Actuator color

Green

Bezel

Silver

Actuator function

Momentary

Button color

Top: green, bottom: red

Actuator

Flush, dual button

Illumination

Illuminated

Series

M22

Environmental rating

IP66, NEMA 4X, NEMA 13

Operating cycles

Light: 100,000, button: 200,000

Size

22.5 mm

Resources

Specifications and datasheets

[Global Data Sheet - M22-DDLF-GR](#)

[Eaton Specification Sheet - M22-DDLF-GR](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton M22-DDLF-GR

Catalog Number: M22-DDLF-GR

Eaton M22 modular pushbutton, 22.5 mm, Flush - dual button actuator, Momentary, Illuminated, Bezel: Silver, Button: Top Green, Bottom Red, IP66, NEMA 4X, 13, Light 100,000 hours, Button 200,000 Operations



Photo is representative

General specifications

Product Name

Eaton M22 modular pushbutton

Catalog Number

M22-DDLF-GR

UPC

786685272191

Product Length/Depth

2.15 in

Product Height

0.52 in

Product Width

1.17 in

Product Weight

0.995 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

CE Marked
GoST-R
Bureau Veritas

Certifications

CSA Certified
CCC Marked
Lloyd's Register Certified

Catalog Notes

Includes contact block mounting adapter.

defaultTaxonomyAttributeLabel

Application

Pushbutton

Special features

M22 series

Type

22.5 mm Modular

Actuator color

Green

Bezel

Silver

Actuator function

Momentary

Button color

Top: green, bottom: red

Actuator

Flush, dual button

Illumination

Illuminated

Series

M22

Environmental rating

IP66, NEMA 4X, NEMA 13

Operating cycles

Light: 100,000, button: 200,000

Size

22.5 mm

Resources

Specifications and datasheets

[Global Data Sheet - M22-DDLF-GR](#)

[Eaton Specification Sheet - M22-DDLF-GR](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)