

Eaton M22-DDLF-GR

Catalog Number: M22-DDLF-GR

Eaton M22 modular pushbutton, 22.5 mm, Flush - dual button actuator, Momentary, Illuminated, Bezel: Silver, Button: Top Green, Bottom Red, IP66, NEMA 4X, 13, Light 100,000 hours, Button 200,000 Operations



Photo is representative

General specifications

Product Name	Catalog Number
Eaton M22 modular pushbutton	M22-DDLF-GR
UPC	Product Length/Depth
786685272191	2.15 in
Product Height	Product Width
0.52 in	1.17 in
Product Weight	Warranty
0.995 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Compliances	Certifications
CE Marked	CSA Certified
GoST-R	CCC Marked
Bureau Veritas	Lloyd's Register Certified
Catalog Notes	
Includes contact block mounting adapter.	

defaultTaxonomyAttributeLabel

Application

Pushbutton

Special features

M22 series

Type

22.5 mm Modular

Actuator color

Green

Bezel

Silver

Actuator function

Momentary

Button color

Top: green, bottom: red

Actuator

Flush, dual button

Illumination

Illuminated

Series

M22

Environmental rating

IP66, NEMA 4X, NEMA 13

Operating cycles

Light: 100,000, button: 200,000

Size

22.5 mm

Resources

Specifications and datasheets

[Global Data Sheet - M22-DDLF-GR](#)

[Eaton Specification Sheet - M22-DDLF-GR](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)