

# Eaton M22-L-G-230G

Catalog Number: M22-L-G-230G

Eaton M22 modular pushbutton, Green Indicating Light, Flush, IP67, IP69K, NEMA 4X, 13, Illuminated, 100, 000 Hours of operation, 85-264 Vac/dc



## General specifications

### Product Name

Eaton M22 modular pushbutton

### Catalog Number

M22-L-G-230G

### UPC

786685278568

### Product Length/Depth

2 in

### Product Height

1 in

### Product Width

2 in

### Product Weight

0.1 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Compliances

RoHS Compliant

GoST-R

Bureau Veritas

CE Marked

### Certifications

CCC Marked

CSA Certified

Lloyd's Register Certified



Powering Business Worldwide

## Product specifications

### Light color

Green

### Series

M22

### Type

Complete Indicating Light

### Operating Cycles

100,000 Hours of operation

### Environmental rating

IP67, IP69K, NEMA 4X, 13

### Illumination

Illuminated

### Lens color

Green

### Size

22.5 mm

### Voltage rating

85-264 Vac/dc

### Actuator

Flush

## Resources

### Brochures

[M22 Pilot Devices](#)

### Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

### Drawings

[M22-L 3D Model Xchange](#)

[M22-L 2D Drawing Xchange](#)

[M22-L 2D PDF](#)

[M22-L AutoCAD 2D Footprint \(mm\)](#)

[M22-L 3D Inventor](#)

[M22-L AutoCAD 2D Footprint](#)

### Installation instructions

[M22 Operators and Accessories](#)

### Specifications and datasheets

[Eaton Specification Sheet - M22-L-G-230G](#)

[Global Data Sheet - M22-L-G-230G](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)